

## FMCN45905 DATA SHEET

# SHV Plug Connector Crimp/Solder Attachment for RG214, RG9, RG225, RG393 Cable

FMCN45905 SHV plug coax connector has an interface type of SHV plug which is compatible with RG214, RG9, RG225 and RG393 cables and has a 50 Ohms impedance. Fairview Microwave's SHV plug connector uses crimp/solder as an attachment method. Our plug SHV coax connector operates at a minimum frequency of DC and a maximum frequency of 300 MHz.

The Fairview Microwave SHV plug coax connector has a PTFE dielectric type and a VSWR of 1.3. Fairview Microwave's SHV coax connector has a brass body with nickel plating. Our FMCN45905 SHV connector uses brass contact. This bayonet RF connector can operate at temperatures ranging from -65 to +165 degrees C. Additional RF connector specs and dimensions for this component can be found on its PDF specification datasheet and CAD drawings above.

This SHV plug RF connector with coax termination and 50 Ohm impedance is designed to be used with RG214, RG9, RG225 and RG393 cables. Our high-quality FMCN45905 connector features a 100 µin minimum body plating specification. This SHV connector has a gold inner contact plating. Fairview Microwave's SHV plug connector has a maximum operating voltage of 3500 Vrms.

This Fairview Microwave plug SHV connector will ship the same business day as purchased. Our SHV plug connector is part of over 40,000 RF, microwave, and millimeter wave components in stock for worldwide shipment. For further information on similar products, our expert technical support and trained sales team can get you the ideal RF connector as per your requirements.

### **Electrical Specifications**

Description	Min	Тур	Max	Units
Frequency Range	DC		300	MHz
VSWR			1.3:1	
Operating Voltage (AC)			3,500	Vrms

#### **Mechanical Specifications**

Size

 Length
 2.11 in [53.59 mm]

 Width/Dia.
 0.57 in [14.48 mm]

 Height
 0.57 in [14.48 mm]

 Weight
 0.051 lbs [23.13 g]

#### **Material Specifications**

Description	Material	Plating	
Contact	Brass	Gold 30 µin minimum	
Insulation	PTFE		
Body	Brass	Nickel 100 µin minimum	
Coupling Nut	Brass	Nickel 100 µin minimum	



## **Configuration:**

- SHV Plug Connector
- MIL-STD-348A
- 50 Ohms
- Straight Body Geometry
- RG214, RG9, RG225, RG393
   Interface Type
- Crimp/Solder Attachment

#### **Features:**

- Operating Frequency of 300 MHz Max.
- Good VSWR of 1.3:1
- Gold Plated Brass Contact
- 30 µin minimum contact plating

## **Applications:**

- General Purpose Test
- Custom Cable Assemblies

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





## **Environmental Specifications Temperature**

Operating Range

-65 to +165 deg C

**Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:

SHV Plug Connector Crimp/Solder Attachment for RG214, RG9, RG225, RG393 Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: SHV Plug Connector Crimp/Solder Attachment for RG214, RG9, RG225, RG393 Cable FMCN45905

URL: https://www.fairviewmicrowave.com/shv-plug-rg214-rg9-rg225-rg393-connector-fmcn45905-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020 REV 1.0 Page 2 of 3





