

Frequency Divider, Divide by 8 Prescaler Module, 100 MHz to 24 GHz, SMA

The FMFD8004 is a Frequency Divider module that operates across a wide input frequency range from 100 MHz to 24 GHz and supports a divide ratio of 8. Output Frequency is 12.5 MHz to 3 GHz. Impressive broadband typical performance includes output power of +2 dBm, and phase noise of -150 dBc/Hz. This exceptional technical performance is achieved through the use of a hybrid MIC PCB solder assembly which is RoHS and REACH compliant. Additional features include internal voltage regulation and reverse voltage protection. This frequency divider design requires +12 Vdc typical bias voltage, operates over maximum temperature range of -40°C to +85°C, and has an absolute maximum rating for input power of +13 dBm. The rugged and compact package supports SMA Female connectors and RFI and Ground Pins. And for highly reliable operation, the model is guaranteed to meet MIL-STD-202 environmental test conditions for Humidity, Shock, Vibration, and Altitude.

Electrical Specifications (TA= 25°C, Vd1 = 12 Vdc, Id1 = 85 mA)

Description	Min	Typ	Max	Units
Input Frequency (Sine Wave)	0.1		24	GHz
Output Frequency (Square Wave Output)	0.0125		3	GHz
Divide by Ratio		8		
Impedance		50		Ohms
Input Power (CW)			10	dBm
Output Power	-2	2		dBm
Phase Noise @100kHz Offset		-150		dBc/Hz
Operating DC Voltage 1	9	12	15	V
Operating DC Current 1		85	100	mA

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	0.1 to 0.3	0.3 to 1	1 to 18	18 to 21	21 to 24	GHz
Input Power (CW), Max	10	10	10	10	10	dBm
Input Power (CW), Min	3	-5	-15	-5	0	dBm

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Output Frequency Range	0.1 to 24					GHz
Output Power (CW), Typ	2					dBm
Output Power (CW), Min	-2					dBm

Absolute Maximum Rating

Mechanical Specifications

Size	
Length	1.25 in [31.75 mm]
Width	1.25 in [31.75 mm]
Height	0.563 in [14.3 mm]
Weight	0.009 lbs [4.08 g]



Features:

- Wide Input Frequency Range 100 MHz to 24 GHz
- Divide-by-2 Prescaler
- Output Frequency 12.5 MHz to 3 GHz
- Output Power +2 dBm typical
- Low SSB Phase Noise -150 dBc/Hz @ 100 KHz offset typical
- RoHS & REACH Compliant Assembly
- Bias Voltage +12 Vdc @ 85mA
- Operational Temperature Range -40°C to +85°C
- Compact SMA Connectorized Package
- Designed to meet MIL-STD-202 Test Conditions
- Reverse Voltage protection
- Internal Voltage Regulation

Applications:

- Aerospace & Defense
- Test & Measurement
- Microwave Radio Systems
- Military & Commercial Communication Systems
- Research & Development
- SATCOM
- Wireless Communications

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Package Type
Output Connector

Connectorized
SMA Female

Environmental Specifications

Temperature

Operating Range -40 to +85 deg C
Storage Range -55 to +105 deg C


Humidity MIL-STD-202, Method 103B, Condition B
Shock MIL-STD-202F, Method 213B, Condition B
Vibration MIL-STD-202F, Method 204D, Condition B
Altitude MIL-STD-202F, Method 105C, Condition B

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data



Frequency Divider, Divide by 8 Prescaler Module, 100 MHz to 24 GHz, SMA from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Frequency Divider, Divide by 8 Prescaler Module, 100 MHz to 24 GHz, SMA FMFD8004](#)

URL: <https://www.fairviewmicrowave.com/sma-frequency-divider-divide-8-prescaler-module-100-mhz-24-ghz-fmfd8004-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

