



# Biased Detector With SMA Male to SMA Female and Negative Video Out Operating From 2 GHz to 4 GHz

The FMMT1003 is a biased Schottky detector that displays an extremely flat frequency response over a broad frequency range from 2 GHz to 4 GHz. The model features Negative video output polarity, with no external DC bias source is required. Additional features include 50 ohm matched inputs, high voltage sensitivity for very small signal detection of 2000 mV/mW typical, and can withstand maximum input power levels up to +23 dBm CW. Operating temperature range is -55°C to +125°C. The compact and rugged cylindrical package supports an SMA male input connector and SMA female output connector and is ideal for use with precision test and measurement, instrumentation, and subsystem assemblies.

## **Electrical Specifications**

Description	Min	Тур	Max	Unit
Frequency Range	2		4	GHz
Flatness		±0.5		dB
Input Power			+23	dBm
Operating Temperature Ra	nge -55		+125	deg C

Electrical Specification Notes:

@ +25 deg C, 100uA Bias, and -20 dBm Pin Voltage Sensitivity is that of an open circuit

TSS is measured with a 2 MHz video bandwidth and a 2 dB NF Amplifier



#### Features:

- · Biased Schottky Diode Detector
- 2 GHz to 4 GHz Frequency Range
- Extremely Flat Frequency Response
- Maximum Input Power +23 dBm
- Negative Video Output Polarity

# **Applications:**

- · Electronic Warfare
- Test & Measurement
- System Monitoring
- AM Noise Measurements
- · Military & Space
- Radar
- Pulsed RF Measurements in Ultra Broadband Applications
- Leveling Pulse Signal Sources
- Military Communications Systems

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

www.fairviewmicrowave.com sales@fairviewmicrowave.com





## **Mechanical Specifications**

Size

 Length
 1.25 in [31.75 mm]

 Width
 0.316 in [8.03 mm]

Weight 0.0215 lbs [9.75 g]

Connector 1 SMA Male Connector 2 SMA Female

#### **Environmental Specifications**

**Temperature** 

Operating Range -55 to +125 deg C Storage Range -65 to +150 deg C

**Compliance Certifications** (see product page for current document)

**Plotted and Other Data** 


Notes:

**Typical Performance Data** 






### TRANSFER CHARACTERISTIC













Biased Detector With SMA Male to SMA Female and Negative Video Out Operating From 2 GHz to 4 GHz from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Biased Detector With SMA Male to SMA Female and Negative Video Out Operating From 2 GHz to 4 GHz FMMT1003


URL: https://www.fairviewmicrowave.com/biased-detector-sma-male-2-4-ghz-fmmt1003-p.aspx







1.21 [30.7] 27 [6.9] 0 31 [7.9] 1/4-36 UNS



SMA FEMALE OUTPUT J2

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  3. DIMENSIONS ARE IN INCHES [mm].					
Biased Detector With SMA Male to SMA Female and	DWG NO FMMT1003			CAGE CODE 3FKR5		
Negative Video Out Operating From 2 GHz to 4 GHz	CAD FILE 110117	SHEET 1 OF 1	SCALE	N/A	SIZE A	7361