

# 0.2 MHz to 3 GHz Surface Mount (SMT) Noise Source Module, Output ENR of 31 dB, +12 VDC, Pin Packaged

The FMNSNS4002 is a surface mount packaged noise source which operates over a frequency range from 200 KHz to 3 GHz. This module is particularly useful in circuit board applications used for built-in test equipment, dithering for increased dynamic range of A/D converters, and as a source for bit error rate testing. This module operates at +12 Vdc and features a high output ENR level of 31 dB. The ouput White Gaussian Noise has a minimum power level of -143 dBm/Hz. Maximum flatness across the entire frequency band is +/-1.50 dB. Operating temperature range is -40°C to +85°C with a temperature coefficient of 0.01 dB/°C. The small surface mount package outline uses 8 gull wing leads. For the circuit board layout, a through hole mounting footprint diagram is included for reference.

#### **Electrical Specifications**

Description	Min	т	ур	Max	Units
Frequency Range	0.0002			3	GHz
Impedance		[	50		Ohms
Output ENR	31				dB
Flatness				±1.5	dB
Supply Voltage Sensitivity	/	С	0.1		dB/%V
Thermal Sensitivity		0	01		dB/deg C
Noise Power Spectral Den	sity -143				dBm/Hz
Bias Voltage 1			12		Volts
Damage Level for Bias 1				24	Volts
Input Current 1				10	mA
Crest Factor		5	:1		

## **Mechanical Specifications**

<b>Size</b> Length Width/Dia. Height	0.815 in [20.7 mm] 0.595 in [15.11 mm] 0.255 in [6.48 mm]
Weight	0.01 lbs [4.54 g]
Package Type	Surface Mount
<b>Connectors</b> DC Connector	Pin
Environmental Specifications Temperature Operating Range	-40 to +85 °C

### Compliance Certifications (see product page for current document)

-65 to +150 °C

## **Plotted and Other Data**

Storage Range

Notes:





# Features:

- Surface Mount Packaged Noise
  Source module
- Frequency Range: 200 KHz to 3 GHz
- High Output ENR level: 31 dB
- White Gaussian Noise Output
- Minimum power level -143 dBm/ Hz
- Maximum Flatness +/- 1.50 dB
- Small Package Outline with 8 gullwing leads
- DC Voltage: +12 Vdc
- -40°C to +85°C Operating Temperature
- Crest Factor: 5:1


# **Applications:**

- Noise Figure Test & Measurment
- Built-In Test Equipment
- Dithering for Increased Dynamic Range for A/D Converters
- Source for Bit Error Rate Testing

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com







#### **Typical Performance Data**

0.2 MHz to 3 GHz Surface Mount (SMT) Noise Source Module, Output ENR of 31 dB, +12 VDC, Pin Packaged from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

Click the following link to obtain additional part information: 0.2 MHz to 3 GHz Surface Mount (SMT) Noise Source Module, Output ENR of 31 dB, +12 VDC, Pin Packaged FMNS4002

URL: https://www.fairviewmicrowave.com/noise-source-enr-31-db-3-ghz-fmns4002-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Fairview Microwave




an INFINIT<sup>®</sup> brand



Fairview Microwave

## an INFINIT<sup>®</sup> brand



FMNS4002

**DATA SHEET** 

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689