

Non-Penetrating Antenna Peak Roof Mount, 1-pole Version, 60-inch Mast, Galvanized Steel with Powder Coating

Fairview Microwave's FMPRM1 non-penetrating antenna peak roof mount is available for different types of roof installations, and it is easy to transport. This 1-pole version communication antenna mount has a 60-inch center mast and doesn't need screws or anchors, which minimizes damage to the roofs. This NPM mount is used for peak roofs and is available with easy assembly instructions.

The FMPRM1 non-penetrating mount has operating windspeeds up to 50 Km/h or 31 MPH and survival windspeeds up to 100 Km/h or 62 MPH. This non-penetrating mount has a strong and rugged design made up of galvanized steel. The roof mount has a powder coating to withstand harsh climates and corrosion.

This FMPRM1 non-penetrating antenna peak roof mount is suitable for telecom installers, DIY installers, satellite dish installers, wireless internet providers, crypto enterprises, and commercial building owners that can be mounted on roofs. Ballast material (i.e., cinder blocks, concrete blocks, etc.) are used in these non-drill roof mounts to anchor them to the roof

Fairview Microwave has one of the largest in-stock selection of non-penetrating antenna peak roof mount for international and domestic orders. Make your online purchase right now to take advantage of our same-day shipping. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the perfect 1-pole version non-penetrating mount for your requirements.

Note: Ballast data should be determined by a local professional engineer. Adequate ballast material must be determined and provided by others



Features:

- Easy assembly instructions
- 5 ft tall center mast
- Secondary arm of 2.75 ft
- Powder coated galvanized steel
- Operating windspeeds up to 50 KM/h (31 mph)
- Survival windspeeds up to 100 KM/h (62 mph)
- All assembly hardware included
- Optional mat for max surface tension/protection
- Standard 16" x 8" cinder blocks (Not included)
- 150-degree max angle for roof pitch

Applications:

- De-centralized wireless networks (FreedomFi, Helium, POLLEN, XNET, MetaBlox, etc.)
- Wireless or satellite antenna
- Scientific and weather instrumentations
- Security camera and instruments
- Solar panel

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Note:



- **Ballast data should be determined by a local professional engineer. Adequate ballast material must be determined and provided by others**
- Prior to installation, verify that the installation, roof material and supporting structures have been investigated and found capable to withstand load
- Place ballast material (i.e., cinder blocks, concrete blocks, etc.) evenly on both side with at least 4 on each side, total 8 blocks per mount approx. 300lbs over all base angles (Estimated Operational Ballast)
- All antenna installations MUST be grounded
- **Fairview Microwave RECOMMENDS THAT BALLAST MATERIAL ALWAYS BE PLACED PRIOR TO MOUNTING ANTENNAS AND THAT THE MOUNT BE SECURED TO PREVENT HAZARDS FROM OCCURRING UNDER EXTREME WIND LOADING CONDITION**
- Inspect all bolts and screws for optimal tightness (recommended torque 13-14 lbs-ft.) to ensure there is no loose gaps after installation
- Recommended to use self -tapping screws provided with mount to reduce the loading of the roof if working environment is allowed to drill
- Inspect the mount, antennas, and tightness of nuts at six-month maximum intervals

Operational	50 Km/h (31 mph)	Under recommended Load
Survival	100 Km/h (62 mph)	Under recommended Load

CONTACT A LOCAL PROFESSIONAL ENGINEER TO DETERMINE PROPER LOADING vs BALLAST WEIGHTS

Operational: It is workable under 50km/h wind speeds.

Survival: The products may be deformed but will not fly away.



Mechanical Specifications

Size

Length	59.84 in [151.99 cm]
Width	4.33 in [109.98 mm]
Height	7.28 in [184.91 mm]
Weight	49.6 lbs [22.5 kg]

Environmental Specifications

Operating Temperature, Min	-40 deg C
Operating Temperature, Max	80 deg C
Wind Velocity	31 MPH [49.89KPH]
Plating	Powder Coat
Material	Galvanized Steel
Package Quantity	1

Non-Penetrating Antenna Peak Roof Mount, 1-pole Version, 60-inch Mast, Galvanized Steel with Powder Coating from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Non-Penetrating Antenna Peak Roof Mount, 1-pole Version, 60-inch Mast, Galvanized Steel with Powder Coating](#)

URL: <https://www.fairviewmicrowave.com/non-penetrating-antenna-peak-roof-mount-1-pole-version-60-inch-mast-galvanized-steel-with-powder-coating-fmprm1-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

