



SMA Mixer from 10 MHz to 1 GHz with an IF Range from DC to 800 MHz and LO Power of +4 dBm

The FMMX1015 is a broadband Double Balanced Mixer that operates across an RF and LO frequency range from 10 MHz to 1000 MHz with an IF frequency range of DC to 800 MHz and supports an LO drive level range from +1 to +7 dBm, with +4 dBm nominal. The design utilizes Schottky Ring Quad Diodes with optimized balun structures. Exceptional typical performance includes Conversion Loss of 7.2 dB, RF to LO and LO to IF isolation levels up to 75 dB, and an input IP3 level of +16 dBm. The 50 ohm hybrid module does not require any external components or matching circuitry. The rugged compact package assembly supports female SMA connectors, operates over a temperature range of -40°C to +85°C, and is designed to meet MIL-STD-202 environmental test conditions for Humidity, Shock, Vibration, and Altitude for high reliability.

Electrical Specifications

Description	Min	Тур	Max	Units
RF Frequency Range	10		1,000	MHz
LO Frequency Range	10		1,000	MHz
IF Frequency Range	DC		800	MHz
Impedance		50		Ohms
Conversion Loss		7.2	8.2	dB
LO to RF Isolation	27	60		dB
LO to IF Isolation	13	33		dB
RF Port VSWR		1.5:1	2:1	
IF Port VSWR		1.5:1	2:1	
Input at IP3	+13	+16		dBm
RF Input Power			+1	dBm
LO Input Power		+4		dBm

Mechanical Specifications

Weight 0.089 lbs [40.37 g]

Configuration

Double Balanced Design Connectorized Package Type **RF** Connector **SMA Female** LO Connector SMA Female **IF** Connector **SMA Female**

Environmental Specifications

Temperature

Operating Range -40 to +85 deg C Storage Range -55 to +100 deg C

Humidity MIL-STD-202F, Method 103B, Condition

В



Features:

- · Broadband Double Balanced Mixer Design
- LO & RF Frequency Range: 10 MHz to 1000 MHz
- · IF Frequency Range: DC to 800 MHz
- LO Drive Level Range: +1 dBm to +7 dBm
- · Schottky Ring Quad Diodes with Optimized Balun Structures
- Conversion Loss: 7.2 dB typ
- High Port Isolations up to 75 dB typ
- Input IP3 Level: +16 dBm
- RF Input Up to +1 dBm
- Operating Temperature Range: -40°C to +85°C
- SMA Connectors / Designed to Meet MIL-STD-202 **Environmental Test Conditions**

Applications:

- Flectronic Warfare
- · Point-to-Point Radios
- Point-to-Multipoint Radios
- VSAT
- Radar
- Space Systems
- Test Instrumentation

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Shock MIL-STD-202F, Method 213B, Condition B Vibration MIL-STD-202F, Method 204D, Condition B Altitude MIL-STD-202F, Method 105C, Condition B

Compliance Certifications (see product page for current document)

Plotted and Other Data

-9 -10


10 MHz

109

208

Notes:

Typical Performance Data




901

1000







SMA Mixer from 10 MHz to 1 GHz with an IF Range from DC to 800 MHz and LO Power of +4 dBm from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: SMA Mixer from 10 MHz to 1 GHz with an IF Range from DC to 800 MHz and LO Power of +4 dBm FMMX1015

URL: https://www.fairviewmicrowave.com/sma-mixer-4-dbm-fmmx1015-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

Fairview Microwave!	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
SMA Mixer from 10 MHz to 1 GHz with an IF Range from DC to 800 MHz and LO Power of +4 dBm	DWG NO FMMX1015			CAGE CODE 3FKR5		
	CAD FILE 04/26/18	SHEET 1 OF 1	SCAL	E N/A	SIZE A	7361