

FMPB1006 DATA SHEET

Coaxial RF GS Probe with 800 Micron Pitch Up to 40 GHz with 2.92mm Interface and Cable Mount

Coaxial RF GS probe, part number FMPB1003, from Fairview Microwave is in-stock and ships same day. This probe is part of a full family of GS (SG) and GSG probe versions that are well suited for PCB probing, device characterization and RF probing on test fixtures. The probes easily connect to a RF coaxial cable to connect RF test equipment, including network analyzers, spectrum analyzers, signal sources or BERTs. While they are designed to be used manually with a coaxial cable assembly, they can also be used with Fairview Microwave's optional probe positioner for added stability and probe repeatability. Differential measurements are also possible by using pairs of RF GS probes in tandem with skew matched cable assemblies.

Fairview's coaxial RF GS probe datasheet specifications and outline drawing are shown in this PDF fellow. Our extensive offering of RF, microwave and millimeter wave interconnects allows designers to configure and customize their signal connections however they like. From making consistent RF probe measurements or probing and characterizing PCBs, Fairview Microwave has the right probing and connection solutions to meet your needs.

Electrical Specifications

Description	Min	Тур	Мах	Units
Frequency Range	DC		40	GHz
Impedance		50		Ohms
Return Loss			10	dB
Insertion Loss			0.5	dB

Mechanical Specifications

Probe Configuration Pin Type Pitch	GS Pogo Pin 800 um [0.03 in]
Connector Connector Type	2.92mm Female
Size Length Weight	1.18 in [29.97 mm] 0.009 lbs [4.08 g]

Environmental Specifications

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:



Configuration:

- Single Channel
- Cable Mount
- •GS Tip
- 2.92mm Female Connector
- 800 um Pitch

Features:

- 40 GHz Performance
- Good Return Loss of 10 dB
- Convenient Cable Mount
- Gold Plated GS Contacts

Applications:


- S-parameter Probing
- RF Coaxial Probing
- Signal Integrity Measurements
- Device Characterization
- Coplanar Waveguide Probing


Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com






Typical Performance Data











FMPB1006 DATA SHEET











FMPB1006 DATA SHEET










Coaxial RF GS Probe with 800 Micron Pitch Up to 40 GHz with 2.92mm Interface and Cable Mount from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Coaxial RF GS Probe with 800 Micron Pitch Up to 40 GHz with 2.92mm Interface and Cable Mount FMPB1006


URL: https://www.fairviewmicrowave.com/coaxial-rf-gs-probe-1500-micron-pitch-40ghz-2.92mm-cable-mountfmpb1006-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.









GHz with 2.92mm Interface and Cable Mount

CAD FILE 07/13/18

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

SHEET

1 OF 1

SCALE N/A

SIZE A

7361