

## SMA Reflective SP4T GaN High Power PIN Diode Switch from DC to 6 GHz Rated at 40 Watts < 100ns Speed

The FMSW1104 is a high power Reflective SP4T PIN Diode Switch that operates from DC to 6 GHz. The module utilizes Gallium Nitride (GaN) and chip-and-wire technology in the manufacturing process that ensures state-of-the-art power performance with excellent power-to-volume ratio that's ideal for broadband high power applications. The 50 ohm reflective design has impressive RF input power handling capability for cold switching up to +46 dBm, and incorporates TTL compatible driver circuitry for accurate logic control. Typical performance includes 1.7 dB insertion loss, 40 dB isolation, 1.35:1 VSWR, and < 100 nsec switching speed. Operational temperature range is -45°C to +85°C and the bias voltage requirement is +12 Vdc. The rugged and compact package supports SMA female connectors and is designed to meet a series of environmental conditions including Altitude, Vibration, Humidity, and Shock. Model FMSW1109 is the same switch design but includes an integrated heatsink.

### Electrical Specifications

TTL Control Logic

 Off/Isolation: 0 to 0.8 V  
 On/Low Loss: 2.8 to 5 V

Description	Min	Typ	Max	Units
Frequency Range	DC		6	GHz
Impedance		50		Ohms
VSWR		1.35:1	1.5:1	
Insertion Loss		1.5	2	dB
IL Temp. Coefficient		0.003		dB/degC
Isolation	25	40		dB
Switching Time			100	ns
P0.1dB		50		dBm
Input IP3		50		dBm
Input Power (CW)			40	Watts
DC Power Dissipation		1		Watt
Positive Operating Voltage		12		Vdc
Current @ 12 Vdc		200		mA
Operating Temperature	-45		+85	deg C

### Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 3	3 to 6				GHz
VSWR, Max	1.3:1	1.5:1				
VSWR, Typ	1.2:1	1.35:1				
Insertion Loss, Max	1.5	2				dB
Insertion Loss, Typ	1	1.7				dB
Isolation, Min	35	25				dB
Isolation, Typ	42	30				dB

Electrical Specification Notes:

Internal TTL Driver will become damaged if Negative Voltage is applied



### Features:

- Reflective SPDT High Power PIN Diode Switch
- GaN Semiconductor Technology
- Reflective Design
- Frequency Range: 500 MHz to 18 GHz
- Insertion Loss: 1.7 dB typ
- Isolation: 40 dB typ
- VSWR: 1.35:1 typ
- Maximum RF Input Power: +46 dBm
- Input IP3: +50 dBm typ
- Switching Speed: < 100 nsec
- TTL Compatible Driver Circuitry
- 50 Ohm Design
- SMA Female Connectors
- Compact Package Design withstands up to 95% Relative Humidity
- -45°C to +85°C Operating Temperature

### Applications:

- Aerospace & Defense
- Microwave Radio
- Military & Commercial Communication
- VSAT
- SATCOM
- Test & Measurement
- Wireless Infrastructure
- Fiber Optics

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

\*Cold Switching: Before changing any TTL signal(s), the RF input power must be blanked or the switch could become damaged

**Absolute Maximum Rating**

Parameter	Rating
Biasing	+12V±10%
TTL Control Voltage	0~0.8V/2.8~5V



ESD Sensitive Material,  
Transport material in  
Approved ESD bags.  
Handle only in approved  
ESD Workstation.

**Mechanical Specifications**

Length	1.97 in [50.04 mm]
Width	1.97 in [50.04 mm]
Height	0.37 in [9.4 mm]
Weight	0.32 lbs [145.15 g]
Design	Reflective, SP4T
RF Connector	SMA Female

**Environmental Specifications**



<b>Temperature</b>	
Operating Range	-45 to +85 deg C
Storage Range	-55 to +125 deg C
Humidity	100% RH @ 35°C, 95% RH @ 40°C
Shock	20G for 11ms Half Sinewave, 3 axis both directions
Vibration	25g RMS (15° 2KHz) endurance, 1 hr per axis
Altitude	30,000 ft. (Epoxy Sealed Controlled Environment)


**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

**Typical Performance Data**





SMA Reflective SP4T GaN High Power PIN Diode Switch from DC to 6 GHz Rated at 40 Watts < 100ns Speed from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [SMA Reflective SP4T GaN High Power PIN Diode Switch from DC to 6 GHz Rated at 40 Watts < 100ns Speed FMSW1104](https://www.fairviewmicrowave.com/sma-sp4t-pin-diode-switch-6-ghz-40-watts-fmsw1104-p.aspx)

URL: <https://www.fairviewmicrowave.com/sma-sp4t-pin-diode-switch-6-ghz-40-watts-fmsw1104-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

