

Broadband 75 Ohm F Male to 75 Ohm F Female Cable 75 Ohm FM-SF200LL75 Coax

The 75 ohm type F male to 75 ohm type F female cable using 75 ohm FM-SF200LL75 coax, part number FMTC604, from Fairview Microwave is in-stock and ships same day. This Fairview type F to type F cable assembly has a male to female gender configuration with 75 ohm flexible FM-SF200LL75 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMTC604 type F male to type F female cable assembly operates to 3 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness. Fairview Microwave's test cables are constructed using our FM-SF200LL75 coax which is optimized for use up to 3 GHz with 75 Ohm F-Type connectors. This flexible coaxial cable has excellent low insertion loss along with a velocity propagation of 70%. The highly flexible cable also reduces the strain applied to your test components, making it easier to route the cables in your test setup or equipment rack. These 3 GHz test cables are available with Male and Female Type-F connectors and are available standard lengths from stock for same day shipment.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

-				
Description	Min	Ту	vp Max	Units
Frequency Range VSWR	DC		3 1.35:1	GHz
Insertion Loss			1.23	_
			4.04	_
Velocity of Propagation		7	0	%
Dielectric Withstanding \	/oltage (AC)		500	Vrms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2	3			GHz
Insertion Loss (Max.)	1.16	1.19	1.23			dB/ft
	3.81	3.9	4.04			dB/m

Electrical Specification Notes: Values at 25°C, sea level.

Mechanical Specifications

Cable Assembly Length*

Cable Cable Type 0 in [0 mm]

FM-SF200LL75



DATA SHEET

FMTC604

Configuration:

- F Male
- F Female
- FM-SF200LL75

Features:

- Max Frequency 3 GHz
- 70% Phase Velocity
- Double Shielded
- FEP Jacket
- Precision 75 Ohm Type F connectors
- VSWR of 1.35:1 to 3 GHz
- 70% velocity of propagation (VoP)
- 100% VSWR tested and Hi-Pot tested to 500 volts
- Very flexible and durable
- Enhanced strain relief, heavy duty booting
- In-stock and same day shipment
- Precision Type F center conductor diameter 0.029"
- Broadband performance

Applications:

- General Purpose
- Laboratory Use
- Production testing
- RF development testing
- General lab testing
- Test rack applications

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com Fairview Microwave

an INFINIT[®] brand



Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1 Shield Layer 2 Jacket Material Jacket Diameter

Solid Copper, Bare PTFE 2 Silver Plated Copper Braid Silver Plated Copper Braid FEP 0.195 in [4.95 mm]

One Time Minimum Bend Radius

1 in [25.4 mm]

75 Ohms

Connectors

Description	Connector 1	Connector 2
Туре	F Male	F Female
Impedance	75 Ohms	75 Ohms
Contact Material & Plating	Beryllium Copper, G	old Beryllium Copper, Gold
Dielectric Type	PTFE	PTFE
Outer Cond Material & Plati	Plating Passivated Stainless Steel	
Body Material & Plating	Passivated Stainless S	iteel Passivated Stainless Steel
Coupling Nut Material & Pla	nting Passivated Stainless S	iteel

Compliance Certifications (see product page for current document)


Plotted and Other Data

- Notes:
- Values at 25°C, sea level.

How to Order

Part Number Configuration:

FMTC604



Example: FMTC604-12 = 12 inches long cable FMTC604-100cm = 100 cm long cable

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689






Broadband 75 Ohm F Male to 75 Ohm F Female Cable 75 Ohm FM-SF200LL75 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Broadband 75 Ohm F Male to 75 Ohm F Female Cable 75 Ohm FM-SF200LL75 Coax FMTC604


URL: https://www.fairviewmicrowave.com/broadband-f-male-f-female-cable-fm-sf200ll75-coax-fmtc604-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







FAIRVIEW MICROWAVE INC.	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
TITLE Broadband 75 Ohm F Male to 75 Ohm F Female Cable 75 Ohm FM-SF200LL75 Coax	DWG NO FMTC604			CAGE CODE 3FKR5		
	CAD FILE 022916	SHEET	SCALE N/	A SIZE A	2233	

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689