

2.2-5 Male (Plug) Termination (Load) 5 Watts DC to 6 GHz, Brass Body, 1.25:1 VSWR

Fairview Microwave's PE6TR1162 is an RF termination (also called RF load or dummy load) that operates from DC to 6 GHz and handles up to 5 Watt (CW). Our 2.2-5 termination / load has a male gender. PE6TR1162 2.2-5 load termination offers 1.25:1 max VSWR.

RF load / terminations are indispensable components in many RF, microwave and millimeter wave systems where signal reflection from unused ports can potentially damage the device or reduce the signal integrity. By using a terminator on an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These termination components are commonly used to terminate devices such as couplers, circulators, and switches. They are also widely used in measurement systems to ensure accurate results. Fairview Microwave offers a huge selection of RF, microwave and millimeter wave terminations up to 65 GHz with excellent performance over the entire operating range and power handling capabilities up to 800 Watt (CW).



Features:

- DC to 6 GHz Frequency Range
- 50 Ohm Impedance
- 2.2-5 Male Coaxial Interface
- Max VSWR 1.25:1
- Max Power 5 Watts (CW)

Applications:

- 5G Cellular bands
- SatCom
- Radar Systems
- Test and Measurement
- Commercial and Military Communication

Electrical Specifications

| Description | Min | Typ | Max | Units |
|--|-----|-----|--------|-------|
| Frequency Range | DC | | 6 | GHz |
| Impedance | | 50 | | Ohms |
| VSWR | | | 1.25:1 | |
| Input Power (CW) | | | 5 | Watts |
| Input Power (Peak) 8% Duty Cycle, 20us PW | | | 50 | Watts |

Mechanical Specifications

Size

| | |
|--------------|--------------------|
| Length | 1.38 in [35.05 mm] |
| Width | 0.63 in [16 mm] |
| Height | 0.63 in [16 mm] |
| Weight | 1.1 lbs [498.95 g] |
| Package Type | Connectorized |

Configuration

| | |
|--------------------|------------|
| Connector | 2.2-5 Male |
| Termination Design | RF Load |

Material Specifications

| Description | Material | Plating |
|---------------------|------------------|-----------------------|
| Connector 1 Contact | Beryllium Copper | Silver |
| Insulation | PTFE | |
| Body | Brass | Copper-Tin-Zinc Alloy |
| Housing | Brass | Tri-Metal |

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Environmental Specifications

Temperature

Operating Range -40 to +75 deg C
Storage Range -50 to +85 deg C

Humidity <95%
Shock IEC 60068-2-27
Vibration IEC 60068-2-6-Fc
Altitude <5000m
Thermal Shock IEC 60068 -2-14-Na

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

2.2-5 Male (Plug) Termination (Load) 5 Watts DC to 6 GHz, Brass Body, 1.25:1 VSWR from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [2.2-5 Male \(Plug\) Termination \(Load\) 5 Watts DC to 6 GHz, Brass Body, 1.25:1 VSWR FMTR1162](#)

URL: <https://www.fairviewmicrowave.com/5-watts-6-ghz-fmtr1162-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

