

Voltage Controlled Oscillator, 4245 MHz to 4335 MHz, Pout +0.5 dBm, Phase Noise of -87 dBc/Hz, 0.5V to 8V Tuning Range, SMA

The FMVC31028 is highly reliable low noise Voltage Controlled Oscillator (VCO) that operates across 4245 MHz to 4335 MHz with a tuning voltage range from 0.5V to 8V. Impressive typical performance includes generated output power of +0.5 dBm, 2nd Harmonic Suppression of -13 dBc, phase noise of -87 dBc/Hz @ 10 KHz offset, and tuning sensitivity of 70 MHz/V. The design incorporates internal voltage regulation and reverse DC protection, with a bias voltage range from +9V to +15V. The rugged and compact coaxial package assembly supports SMA female connectors, RFI and ground pins. The VCO has an operational temperature range of -40°C to +85°C and is designed to meet a variety of MIL-STD-202 test conditions including shock, vibration, altitude, and humidity.

Electrical Specifications

| Description | Min | Typ | Max | Units |
|---------------------------|-------|------|-------|--------|
| Frequency Range | 4.245 | | 4.335 | GHz |
| Tuning Voltage | 0.5 | | 8 | Vdc |
| Supply Voltage (DC) | 9 | 12 | 15 | Vdc |
| Supply Current (DC) | | 25 | | mA |
| Phase Noise @10kHz Offset | | -87 | | dBc/Hz |
| Output Power | -2 | +0.5 | +3 | dBm |
| Tuning Sensitivity (Kvco) | | 70 | | MHz/V |
| Pulling (pk-pk) | | | 10 | MHz |
| Load Impedance | | 50 | | Ohms |
| 2nd Harmonics | | -13 | | dBc |

Mechanical Specifications

| | |
|------------------|--------------------|
| Size | |
| Length | 1.25 in [31.75 mm] |
| Width | 1.25 in [31.75 mm] |
| Height | 0.563 in [14.3 mm] |
| Weight | 0.4 lbs [181.44 g] |
| Design | Commercial |
| Connector Option | Standard |
| Output Connector | SMA Female |

Environmental Specifications

| | |
|--------------------|--|
| Temperature | |
| Operating Range | -40 to +85 deg C |
| Storage Range | -55 to +100 deg C |
| Humidity | MIL-STD-202, Method 103B, Condition B |
| Shock | MIL-STD-202F, Method 213B, Condition B |
| Vibration | MIL-STD-202F, Method 204D, Condition B |
| Altitude | MIL-STD-202F, Method 105C, Condition B |



Features:

- Voltage Controlled Oscillator
- 4245 MHz to 4335 MHz
- 0.5V to 8V Tuning Voltage
- Pout: +0.5 dBm
- Phase Noise: -87 dBc/Hz
- 2nd Harmonic Suppression: -13 dBc typ
- Tuning Sensitivity: 70 MHz/V
- +12 Volt DC Bias
- SMA Female Connectors
- -40°C to +85°C Operating Temperature
- 50 Ohm Design
- Internal Voltage Regulation
- Reverse DC Protection
- Rugged Package Design meets Mil-STD-202 Test Conditions

Applications:



- Phase Locked Loop
- Function Generators
- Frequency Synthesizers
- Receivers
- Electronic Jamming Equipment
- Local Oscillators
- Wireless Communications
- SATCOM
- Optical Communications
- Military Electronic Systems

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Typical Performance Data



Voltage Controlled Oscillator, 4245 MHz to 4335 MHz, Pout +0.5 dBm, Phase Noise of -87 dBc/Hz, 0.5V to 8V Tuning Range, SMA


Voltage Controlled Oscillator, 4245 MHz to 4335 MHz, Pout +0.5 dBm, Phase Noise of -87 dBc/Hz, 0.5V to 8V Tuning Range, SMA

Voltage Controlled Oscillator, 4245 MHz to 4335 MHz, Pout +0.5 dBm, Phase Noise of -87 dBc/Hz, 0.5V to 8V Tuning Range, SMA from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Voltage Controlled Oscillator, 4245 MHz to 4335 MHz, Pout +0.5 dBm, Phase Noise of -87 dBc/Hz, 0.5V to 8V Tuning Range, SMA FMVC31028](#)

URL: <https://www.fairviewmicrowave.com/vco-voltage-controlled-oscillator-4.335-ghz-fmvc31028-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



Voltage Controlled Oscillator, 4245 MHz to 4335 MHz,
Pout +0.5 dBm, Phase Noise of -87 dBc/Hz, 0.5V to
8V Tuning Range, SMA