

## N Female (Jack) Termination (Load) 10 Watts to 12.4 GHz, Aluminum Body, 1.35:1 VSWR

Fairview Microwave's FMTR1139 is an RF termination (also called RF load or dummy load) that operates from DC to 12.4 GHz and handles up to 10 Watt (CW). Our N termination / load has a female gender. FMTR1139 N load termination offers 1.35:1 max VSWR.

RF load / terminations are indispensable components in many RF, microwave and millimeter wave systems where signal reflection from unused ports can potentially damage the device or reduce the signal integrity. By using a terminator on an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These termination components are commonly used to terminate devices such as couplers, circulators, and switches. They are also widely used in measurement systems to ensure accurate results. Fairview Microwave offers a huge selection of RF, microwave and millimeter wave terminations up to 65 GHz with excellent performance over the entire operating range and power handling capabilities up to 800 Watt (CW).

### Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		12.4	GHz
Impedance		50		Ohms
VSWR			1.35:1	
Input Power (CW) Derated linearly to 1W at 125°C			10	Watts
Input Power (Peak) 5 $\mu$ s pulse, 1% Duty Cycle			1	kWatts

### Mechanical Specifications

Size	
Length	2.2 in [55.88 mm]
Width	1.5 in [38.1 mm]
Height	1.5 in [38.1 mm]
Weight	0.19 lbs [86.18 g]

### Configuration

Connector	N Female
-----------	----------

### Material Specifications

Description	Material	Plating
Connector 1 Contact	Beryllium Copper	Gold
Body	Black Anodized Aluminum	
Housing	Black Anodized Aluminum	

### Environmental Specifications

Temperature Operating Range	-55 to +85 deg C
--------------------------------	------------------



### Features:

- DC to 12.4 GHz Frequency Range
- 50 Ohm Impedance
- SMA Male Coaxial Interface
- Max VSWR 1.3:1
- Max Power 10 Watts (CW)

### Applications:

- Instrumentation
- Precision Measurements
- Prototyping and Characterization
- Productions Systems
- WIFI 6E
- 5G Cellular Bands

Fairview Microwave  
301 Leora Ln., Suite 100  
Lewisville, TX 75056  
Tel: 1-800-715-4396 / (972) 649-6678  
Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

N Female (Jack) Termination (Load) 10 Watts to 12.4 GHz, Aluminum Body, 1.35:1 VSWR from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [N Female \(Jack\) Termination \(Load\) 10 Watts to 12.4 GHz, Aluminum Body, 1.35:1 VSWR FMTR1139](#)

URL: <https://www.fairviewmicrowave.com/rf-load-10-watts-12.4-ghz-n-female-fmtr1139-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

