

VCO (Voltage Controlled Oscillator) 0.5 inch SMT (Surface Mount), Frequency of 1.2 GHz to 1.8 GHz, Phase Noise -89 dBc/Hz

FMVC11018 is a High Reliability Low Noise Voltage Controlled Oscillator (VCO) which covers a 1200 MHz to 1800 MHz frequency band with a voltage tuning range from 0.0V to 20V. This design features exceptional phase noise performance of -89 dBc/Hz @ 10 kHz offset. Supply Voltage is +15V with a generated output power level of +11.0 dBm and 2nd harmonic output of -12 dBc typical. The assembly is RoHs compliant and available in a compact 0.5 inch SMT package with an industry standard mounting footprint. The bottom surface is copper clad with 2-5 micro inches of immersion Gold over 150 - 250 micro inches of Electro less Nickel which makes it resistant to oxidation for ease of soldering. The VCO operates over a temperature range of -40°C to +85°C and is designed to meet a variety of MIL-STD-202 test conditions including Humidity, Shock, and Vibration.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	1.2		1.8	GHz
Tuning Voltage	0		20	Vdc
Supply Voltage (DC)	14	15	16	Vdc
Supply Current (DC)		20	23	mA
Phase Noise @10kHz Offset		-89	-87	dBc/Hz
Phase Noise @100kHz Offset		-110	-108	dBc/Hz
Output Power	+9.5	+11	+13.5	dBm
Tuning Sensitivity (Kvco)	12		85	MHz/V
Pushing		0.5	1	MHz/V
Pulling (pk-pk)		3	5	MHz
Tuning Port Capacitance		22		pF
Load Impedance		50		Ohms
2nd Harmonics		-12	-10	dBc

Mechanical Specifications

Size	
Length	0.5 in [12.7 mm]
Width	0.5 in [12.7 mm]
Height	0.13 in [3.3 mm]
Weight	0.011 lbs [4.99 g]
Body Material and Plating	Copper Clad Nickel, Gold
Design	Commercial

Environmental Specifications

Temperature	
Operating Range	-40 to +85 deg C
Storage Range	-55 to +125 deg C
Humidity	MIL-STD-202, Method 103, 90% RH, +65 C
Shock	MIL-STD-202, Method 213I
Vibration	MIL-STD-202, Method 204D
Temperature Cycle	MIL-STD-202, Method 107B



Features:

- 1200 to 1800 MHz Bandwidth
- -89 dBc/Hz @ 10kHz offset
- Tuning Voltage 0.0V to 20V
- Pout = +11.0 dBm
- Harmonics = -12 dBc
- RoHs Compliant Assembly
- 0.5" SMT package
- Industry Standard Mounting Footprint
- Designed to meet MIL-STD-202 Environmental Conditions

Applications:

- Phase Locked Loop
- Function Generators
- Frequency Synthesizers
- Receivers
- Electronic Jamming Equipment
- Local Oscillator
- Wireless Communications
- SATCOM
- Optical Communications
- Military Electronic Systems

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

ESD Sensitivity



ESD Sensitive Material, Transport material in Approved ESD bags. Handle only in ESD Workstation.





Compliance Certifications (see [product page](#) for current document)


Plotted and Other Data

Typical Performance Data





VCO (Voltage Controlled Oscillator) 0.5 inch SMT (Surface Mount), Frequency of 1.2 GHz to 1.8 GHz, Phase Noise -89 dBc/Hz







VCO (Voltage Controlled Oscillator) 0.5 inch SMT (Surface Mount), Frequency of 1.2 GHz to 1.8 GHz, Phase Noise -89 dBc/Hz

VCO (Voltage Controlled Oscillator) 0.5 inch SMT (Surface Mount), Frequency of 1.2 GHz to 1.8 GHz, Phase Noise -89 dBc/Hz from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [VCO \(Voltage Controlled Oscillator\) 0.5 inch SMT \(Surface Mount\), Frequency of 1.2 GHz to 1.8 GHz, Phase Noise -89 dBc/Hz FMVC11018](#)

URL: <https://www.fairviewmicrowave.com/vco-voltage-controlled-oscillator-smt-surface-mount-1.8-ghz-fmvc11018-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.




SIDE VIEW

NOTES:

1. THE CASE IS GROUND.
2. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES [mm].
3. UNLESS OTHERWISE SPECIFIED FINISH IS 150-250 MICRO INCHES ELECTROLESS NICKEL OVER COPPER CLAD PCB, 2-5 MICRO INCHES IMMERSION GOLD, OVER NICKEL.
4. MOD PORT NOT AVAILABLE ON ALL MODELS.

FAIRVIEW MICROWAVE INC.		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		DWG NO FMVC11018		CAGE CODE 3FKR5	
TITLE VCO (Voltage Controlled Oscillator) 0.5 inch SMT (Surface Mount), Frequency of 1.2 GHz to 1.8 GHz, Phase Noise -89 dBc/Hz		CAD FILE 020316	SHEET	SCALE N/A	SIZE A 2233



PAD DETAIL


Pin	Con.
1	Vcc
5	RF
13	Vt
Others	GND

PCB PAD LAYOUT

NOTES:

1. THE CASE IS GROUND.
2. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES [mm].
3. UNLESS OTHERWISE SPECIFIED FINISH IS 150-250 MICRO INCHES ELECTROLESS NICKEL OVER COPPER CLAD PCB, 2-5 MICRO INCHES IMMERSION GOLD, OVER NICKEL.
4. MOD PORT NOT AVAILABLE ON ALL MODELS.

FAIRVIEW MICROWAVE INC.		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		DWG NO FMVC11018		CAGE CODE 3FKR5	
TITLE VCO (Voltage Controlled Oscillator) 0.5 inch SMT (Surface Mount), Frequency of 1.2 GHz to 1.8 GHz, Phase Noise -89 dBc/Hz		CAD FILE 020316	SHEET	SCALE N/A	SIZE A 2233



Item	Condition
Tip Temp. (max.)	260°
Iron Power (max.)	20 W
Time (max.)	3 Sec.
Note.	Avoid excess pressure to castelations

Pkg.	tp (°C)
FMVC Series	260
FMVC11 Series	245
All Others	245

NOTES:

1. ALL VCO'S HAVE A MS RATING OF 1
2. ALL PRODUCTS CONFORM TO JEDEC J-STD-020C FOR LEAD FREE PROCESSING.

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE VCO (Voltage Controlled Oscillator) 0.5 inch SMT (Surface Mount), Frequency of 1.2 GHz to 1.8 GHz, Phase Noise -89 dBc/Hz		DWG NO FMVC11018		CAGE CODE 3FKR5	
CAD FILE	020316	SHEET	SCALE	N/A	SIZE A 2233