

## 15 dBi WR-284 Standard Gain Horn Radome Cover

FMWGCOV284-15 is a radome cover for 15 dBi WR-284 Standard Gain Horn antenna. This waveguide antenna radome cover is made from high strength, thermally stable Polymethacrylimide (PMI). PMI offers a low Relative Permittivity (Dielectric Constant) at the high frequency ranges seen with microwave and millimeter wave components. This allows for minimal signal loss or attenuation over other materials.

Increase your system capabilities with our PMI radome covers, designed to enhance the durability and longevity of standard gain horn antennas. Shielding against environmental elements, our radome covers ensure consistent signal integrity in any conditions. FMWGCOV284-15 has internal dimensions of 7.85 in by 5.7 in and will fit 15 dBi WR-284 standard gain horns. Fairview Microwave offers a wide selection of high performance waveguide components available in stock and same-day shipping to customers worldwide.

### Mechanical Specifications

|               |                          |
|---------------|--------------------------|
| Body Material | Polymethacrylimide (PMI) |
| Length        | 8.098 in [205.69 mm]     |
| Width         | 5.941 in [150.9 mm]      |
| Height        | 0.315 in [8 mm]          |
| Weight        | 0.185 lbs [83.91 g]      |

| Mechanical Performance               |                            |                           |                        |                       |                         |                        |                       |                  |
|--------------------------------------|----------------------------|---------------------------|------------------------|-----------------------|-------------------------|------------------------|-----------------------|------------------|
| Typical Density (kg/m <sup>3</sup> ) | Compressive Strength (MPa) | Compression Modulus (MPa) | Tensile Strength (MPa) | Tensile Modulus (MPa) | Fracture Growth Rate(%) | Bending Strength (MPa) | Bending Modulus (MPa) | Deflection (MPa) |
| 200                                  | 8.5                        | 317                       | 7.5                    | 410                   | 2.4                     | 13                     | 449                   | 22               |
| Standard Test                        | GB/T 8813-2008             |                           | GB/T9641-1988          |                       |                         | GB/T 8812.2-2007       |                       |                  |

### Features:

- 15 dBi WR-284 Waveguide Standard Gain Horn
- Polymethacrylimide
- Low Relative Permittivity (Dielectric Constant)
- Minimal reflection or attenuation of signal



| Electrical Performance               |           |      |     |      |      |      |      |  |            |
|--------------------------------------|-----------|------|-----|------|------|------|------|--|------------|
| Antenna Radome Material              | Frequency |      |     |      |      |      |      |  | Tolerance  |
|                                      | 2         | 2.5  | 2.8 | 5    | 10   | 26   | 26.5 |  |            |
| $\epsilon_r$ (Relative Permittivity) | 1.08      | 1.09 | /   | 1.14 | 1.14 | 1.14 | 1.12 |  | $\pm 0.01$ |

Remarks:

1. Test method: GB/T - 5597 - 1999 "Test Method for Microwave Complex Permittivity of Solid Dielectric".
2. Sample size: diameter 51mm, thickness 5mm.
3. Sampling rate and data processing: 5 samples were tested for each material, each sample was tested on both sides, and a total of 80 samples were obtained for each material. data points, and take the average to obtain the final data.

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

**Compliance Certifications** (see [product page](#) for current document)

15 dBi WR-284 Standard Gain Horn Radome Cover from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [15 dBi WR-284 Standard Gain Horn Radome Cover FMWGCov284-15](#)

URL: <https://www.fairviewmicrowave.com/15-dbi-wr-284-standard-gain-horn-radome-cover-fmwgcov284-15-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



