Fairview Microwave

an INFINIT[®] brand

Precision Calibrated, Output Isolator WR-19 Waveguide Noise Source Module, Output ENR of 15 dB, +28 VDC, 40 GHz to 60 GHz

The FMWNS2002 is a U Band waveguide Noise Source module with output Isolator that operates over the full frequency range of 40 GHz to 60 GHz. The benefit of the output Isolator results in improved output port matching for more accurate measurements as well as protection of the noise diode from incident RF power. The microstrip assembly incorporates a millimeter wave noise diode screened for superior noise characteristics that results in highly stable and reliable performance. This module can be used in built-in test and laboratory applications, and can replace outdated gas tube noise sources. Additional applications include noise figure measurements, millimeter wave radiometers, automotive radar, and reserach and development in mm-wave broadband wireless communication systems. The design operates at +28 Vdc with an output ENR level of 15 dB min and a noise output variation of < 0.01 dB/°C, < 0.1 dB/%V. Maximum Flatness across the frequency band is +/- 2 dB and output VSWR is 1.3:1 max with the isolator. Operating temperature range is 0°C to +85°C. The rugged package supports a WR-19 waveguide interface and a BNC connector for the DC voltage supply.

Electrical Specifications

Description	Min	Т	ур	Max	U	Inits
Frequency Range	40			60		GHz
Impedance		Ę	50		С	hms
Output ENR	15					dB
Flatness				±2		dB
VSWR				1.6:1		
Supply Voltage Sensitivity				0.1	d	3/%V
Thermal Sensitivity		0.		0.01	dB/°C	
Bias Voltage 1		2	28		Volts	
Input Current 1				30	mA	

Mechanical Specifications

Package Type

ckage type

Connectorized Module

Environmental Specifications

Temperature

Operating Range

0 to +85 °C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:



Features:

- WR-19 Waveguide Noise Source with Ouput Isolator
- U Band Frequency Range: 40 GHz to 60 GHz
- Output ENR Level: 15 dB min
- Noise Output Variation: < 0.01 dB/oC , < 0.1 dB/%V
- Flatness +/- 2 dB max
- DC Voltage: +28 Vdc
- 0°C to +85°C Operating Temperature
- VSWR: 1.3:1 Max

Applications:


- Noise Figure Test & Measurement
- Built-In Test Applications
- Laboratory Applications
- mm-Wave Radiometers
- Automotive Radar
- R&D for Broadband mm-Wave
 Wireless Communication Systems

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com

FMWNS2002 DATA SHEET







Typical Performance Data

Precision Calibrated, Output Isolator WR-19 Waveguide Noise Source Module, Output ENR of 15 dB, +28 VDC, 40 GHz to 60 GHz from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

Click the following link to obtain additional part information: Precision Calibrated, Output Isolator WR-19 Waveguide Noise Source Module, Output ENR of 15 dB, +28 VDC, 40 GHz to 60 GHz FMWNS2002

URL: https://www.fairviewmicrowave.com/wr-19-precision-waveguide-calibrated-noise-source-enr-15-db-60-ghz-fmwns2002-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Fairview Microwave







301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689