

Broadband Gain Horn Antenna, 18 GHz to 50 GHz
15 dBi Gain, 2.4mm Female Connector

The FMWAN1155 broadband gain horn antenna (double ridge waveguide horn) from Fairview is part of our comprehensive selection of waveguide antennas. This broadband horn features a 2.4mm Female coaxial connector and operates from 18 to 50 GHz.

Our FMWAN1155 broadband gain horn antenna has a nominal gain of 15 dBi with a typical input VSWR of 1.5:1. Fairview's double-ridge broadband horns are available in 10, 11, 13, 15, and 20 dBi models with varying cross band frequency ranges to suit all application needs.

Waveguide antennas, such as the FMWAN1155 are used in a wide variety of applications due to the high-power handling capability, low loss, high directivity, and near constant electrical performance. Our double ridge waveguide antennas with 2.4mm Female interface are part of over 40,000 RF, microwave, and millimeter wave components from Fairview available worldwide and Ship same day.

Configuration

Pattern	Directional
Polarization	Linear
Antenna Design Type	Broadband Gain Horn
RF Connector	2.4mm Female

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	18		50	GHz
Gain		15		dBi
VSWR		1.5:1		

Mechanical Specifications


Size	
Length	1.25 in 31.75 mm
Width	1.17 in 29.72 mm
Height	2.8 in 71.12 mm
Weight	0.144 lbs 65.32 g
Body Material and Plating	Aluminum, Powder Coat
RF Connector	2.4mm Female

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:



Features:


- Antenna Measurements
- Laboratory Use
- Microwave Testing
- Radome Testing
- EMC measurement
- Satellite Antenna Testing
- Radar Cross Section


Applications:

- Ultra Broadband 18 GHz to 50 GHz
- Double-Ridge Waveguide
- Linearly Polarized
- 15 dBi Nominal Gain
- 2.4mm Female Connector
- Mounting Bracket Included
- Powder Coated Aluminum


Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Typical Performance Data







3dB beamwidth (°): E plane: 38.08 H plane: 36.5



3dB beamwidth (°): E plane: 37.6 H plane: 26.7




3dB beamwidth (°): E plane: 32 H plane: 22.8



3dB beamwidth (°): E plane: 22.8

H plane: 18.9



3dB beamwidth (°): E plane: 20.32

H plane: 18.5

Broadband Gain Horn Antenna, 18 GHz to 50 GHz 15 dBi Gain, 2.4mm Female Connector from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Broadband Gain Horn Antenna, 18 GHz to 50 GHz 15 dBi Gain, 2.4mm Female Connector FMWAN1155](https://www.fairviewmicrowave.com/waveguide-horn-antenna-flange-15dbi-50-ghz-fmwan1155-p.aspx)

URL: <https://www.fairviewmicrowave.com/waveguide-horn-antenna-flange-15dbi-50-ghz-fmwan1155-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

