

Broadband Horn Antenna, Dual Polarized 18 GHz to 40 GHz 15 dBi Gain, 2.92mm Female Connector

The FMWAN1167 dual polarized broadband horn antenna (also known as a quad ridge horn antenna) from Fairview Microwave is part of our comprehensive selection of broadband antennas. This quad-ridge waveguide horn features dual 2.92mm Female coaxial connector and operates from 18 GHz to 20 GHz.

Our FMWAN1167 dual polarized broadband horn antenna has a nominal gain of 15 dBi with a typical input VSWR of 1.5:1. Fairview Microwave's broadband horns are available with gain values from 6 to 21 dBi with varying frequency ranges to suit the application needs.

Quad ridge horn antennas, such as the FMWAN1167 are used in a wide variety of applications due to the high-power handling capability, low loss, high directivity, and near constant electrical performance. Our broadband antennas are part of over 40,000 RF, microwave, and millimeter wave components from Fairview Microwave available worldwide and ship same day.

Configuration

Pattern	Directional
Polarization	Dual Linear
Antenna Design Type	Broadband Gain Horn
RF Connector	2.92mm Female

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	18		20	GHz
Gain		15		dBi
VSWR		1.5:1		


Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	18 to 22	22 to 26	26 to 30	30 to 35	25 to 40	GHz
Gain, Typ	13	14	14.5	15	15.5	dB

Mechanical Specifications

Size	
Length	1.377953 in 35 mm
Width	1.377953 in 35 mm
Height	2.440945 in 62 mm
Weight	0.185 lbs 83.91 g
Body Material and Plating	Aluminum
RF Connector	2.92mm Female

Environmental Specifications



Features:

- Ultra Broadband 18 GHz to 20 GHz
- Quad-Ridge Waveguide
- Dual Polarized
- 15 dBi Nominal Gain
- Dual 2.92mm Female Coaxial Connector
- Mounting Bracket Included
- Powder Coated Aluminum

Applications:

- Antenna Measurements
- Laboratory Use
- Microwave Testing
- Radome Testing
- EMC measurement
- Satellite Antenna Testing
- Radar Cross Section


Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com


Compliance Certifications (see [product page](#) for current document)


Plotted and Other Data

Notes:

Typical Performance Data







Broadband Horn Antenna, Dual Polarized 18 GHz to 40 GHz 15 dBi Gain, 2.92mm Female Connector from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Broadband Horn Antenna, Dual Polarized 18 GHz to 40 GHz 15 dBi Gain, 2.92mm Female Connector FMWAN1167](https://www.fairviewmicrowave.com/waveguide-horn-antenna-flange-15dbi-20-ghz-fmwan1167-p.aspx)

URL: <https://www.fairviewmicrowave.com/waveguide-horn-antenna-flange-15dbi-20-ghz-fmwan1167-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

