



### **RG393 Flexible Coax Cable Tan FEP Jacket**

# **Electrical Specifications**

Description	Min	Тур	Max	Units
Frequency Range	DC		10	GHz
Impedance		50		Ohms
Velocity of Propagation		70		%
Nominal Capacitance		29.4		pF/ft
		[96.46]		[pF/m]

# **Performance by Frequency Band**

,		-,				
Description	F1	F2	F3	F4	F5	Units
Frequency	0.01	0.1	1	5	10	GHz
Attenuation, Typ	0.6 1.97	2.1 6.89	7.5 24.61	21 68.9	35 114.83	dB/100ft
Power In (CW), Max	25,000	6,300	1,700	620	350	Watts

# **Mechanical Specifications**

Diameter Weight 0.39 in [9.91 mm]

0.1575 lbs/ft [0.23 Kg/m]

#### **Construction Specifications**

Description	<b>Material and Plating</b>	Diameter			
Inner Conductor	Copper, Silver, 7 Strands	0.094 in [2.39 mm]			
Conductor Type	Stranded				
Dielectric	PTFE	0.285 in [7.24 mm]			
First Shield	Silver Plated Copper Braid 90% coverage	0.313 in [7.95 mm]			
Second Shield	Silver Plated Copper Braid 90% coverage	0.341 in [8.66 mm]			
Jacket	FEP, Tan	0.39 in [9.91 mm]			

# **Environmental Specifications**

**Temperature** 

Operating Range -55 to +200 deg C

**Compliance Certifications** (see product page for current document)

# **Plotted and Other Data**

Notes:



# **Configuration:**

- Flexible Cable
- 2 Shield(s)

#### Features:

- 50 Ohm Impedance
- Stranded Silver Plated Copper Center Conductor
- PTFE Dielectric
- Double Silver Plated Copper Braid
- FEP Jacket Material 0.390 in Diameter

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





RG393 Flexible Coax Cable Tan FEP Jacket from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order

Click the following link to obtain additional part information: RG393 Flexible Coax Cable Tan FEP Jacket RG393

URL: https://www.fairviewmicrowave.com/rg393-flexible-coax-cable-fep-jacket-rg393-p.aspx

	ient improv											
	l specificat											
suitability	of the par	t describ	ed hereir	n for any	y particular	purpose,	and Fair	view Mi	crowave	does no	t assume a	ny liability
arising ou	it of the us	e of any	part or do	ocument	ation.							





