

# **1 dB Fixed Attenuator BNC Male To BNC Female Up To 3 GHz Rated To 2 Watts With Brass Nickel Body**

Fairview Microwave carries a broad selection of fixed attenuators with a wide range of attenuation levels, frequency ranges, and power dissipation ranges. Also known as RF pads, RF microwave attenuators lower the amplitude of a signal (or attenuate) a known amount. These attenuator pads can be used in a wide variety of applications including reducing a signal level to protect measurement equipment or other circuitry, extending the range of power meters and amplifiers, and impedance matching circuits by reducing the VSWR seen by adjacent components. RF attenuators can prevent signal overload in amplifiers, receivers and detectors, adjusting the signal level to a range that is optimal.

Few RF components are as commonly used as fixed coaxial attenuators, and Fairview Microwave carries one of the largest in-stock selections and ships them same day. The SA03B-01 is a 1 dB Fixed Attenuator that operates from DC to 3 GHz and is rated to 2 Watts. The versatile coaxial package uses BNC male to BNC female connectors and is also REACH and RoHS compliant.

#### **Electrical Specifications**

Description	Min	Тур	Мах	Units
Frequency Range	DC		3	GHz
Impedance		50		Ohms
Nominal Attenuation		1		dB
Attenuation Accuracy		±0.5		dB
Input Power, CW			2	Watts

# Contraction ave

SA03B-01

**DATA SHEET** 

## Features:

- DC to 3 GHz Frequency Range
- Attenuation 1±0.5 dB
- Max Power 2 Watts (CW)
- VSWR 1.3:1

# **Applications:**

- Instrumentation
- Precision measurements
- Prototyping and characterization
- Production systems

#### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Range	DC to 2	2 to 3				GHz
VSWR, Typ	1.2:1	1.3:1				

#### **Mechanical Specifications**

Size Length Width/Diameter Weight Body Material and Plating

#### Configuration

Design Package Style 1.8 in [45.72 mm] 0.59 in [14.99 mm] 0.054 lbs [24.49 g] Brass, Nickel

Fixed Connectorized Module

> Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





#### Connectors

Description	Connector 1	Connector 2		
Туре	BNC Male	BNC Female		
Connection Method	Standard	Standard		
Polarity	Standard	Standard		
Contact Material & Plating	Brass, Gold	Beryllium Copper, Gold		
Dielectric Type	PTFE	PTFE		
Body Material & Plating	Brass, Nickel	Brass, Nickel		

### **Environmental Specifications**


 Compliance Certifications (visit www.FairviewMicrowave.com for current document)

 RoHS Compliant
 Yes

 REACH Compliant
 12/17/2015


## **Plotted and Other Data**

Notes:










#### **Typical Performance Data**



1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689






1 dB Fixed Attenuator BNC Male To BNC Female Up To 3 GHz Rated To 2 Watts With Brass Nickel Body from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: 1 dB Fixed Attenuator BNC Male To BNC Female Up To 3 GHz Rated To 2 Watts With Brass Nickel Body SA03B-01

URL: http://www.fairviewmicrowave.com/1db-fixed-attenuator-bnc-male-bnc-female-2-watts-sa03b-01-p.aspx









\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
1 dB Fixed Attenuator BNC Male To BNC Female Up To 3 GHz Rated To 2 Watts With Brass Nickel Body	DWG NO SA03B			CAGE CODE 3FKR5		
	CAD FILE 030116	SHEET	SCAL	E N/A	SIZE A	3045

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689