

30 dB Fixed Attenuator SMP Male Full Detent to SMP Female Up to 10 GHz Rated to 2 Watts with Passivated Stainless Steel Body

Fairview Microwave carries a broad selection of fixed attenuators with a wide range of attenuation levels, frequency ranges, and power dissipation ranges. Also known as RF pads, RF microwave attenuators lower the amplitude of a signal (or attenuate) a known amount. These attenuator pads can be used in a wide variety of applications including reducing a signal level to protect measurement equipment or other circuitry, extending the range of power meters and amplifiers, and impedance matching circuits by reducing the VSWR seen by adjacent components. RF attenuators can prevent signal overload in amplifiers, receivers and detectors, adjusting the signal level to a range that is optimal.

Few RF components are as commonly used as fixed coaxial attenuators, and Fairview Microwave carries one of the largest in-stock varieties and ships them same day. The SA10P2W-30 is a 30 dB Fixed Attenuator that operates from DC to 10 GHz and is rated to 2 Watts. The versatile coaxial package uses SMP male to SMP female connectors and is also REACH and RoHS compliant.



Features:

- DC to 10 GHz Frequency Range
- Attenuation 1±0.5 dB
- Max Power 2 Watts (CW)
- VSWR < 1.40:1

Applications:

- Instrumentation
- Precision measurements
- Prototyping and characterization
- Production systems

Electrical Specifications

| Description | Min | Typ | Max | Units |
|--------------------------------|-----|-----|-------|-------|
| Frequency Range | DC | | 10 | GHz |
| Impedance | | 50 | | Ohms |
| Nominal Attenuation | | 30 | | dB |
| VSWR | | | 1.4:1 | |
| Input Power, CW | | | 2 | Watts |
| Input Power, Peak for 25 µsec. | | | 100 | Watts |

Specifications by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|---------------------|---------|--------|---------|----|----|-------|
| Range | DC to 2 | 2 to 5 | 5 to 10 | | | GHz |
| VSWR, Max | 1.15:1 | 1.25:1 | 1.4:1 | | | |
| Atten Accuracy, Typ | ±0.3 | ±0.5 | ±1 | | | dB |

Electrical Specification Notes:

Impedance deviation of ±0.25 Ohms

VSWR deviation of ±0.1 %

Power coefficient of 0.001 dB/W (change in attenuation with increase in power)

Temperature coefficient of 0.001 dB/°C max., 0.0003 dB/°C typ.

Mechanical Specifications

Size

| | |
|---------------------------|----------------------------|
| Length | 0.81 in [20.57 mm] |
| Width/Diameter | 0.28 in [7.11 mm] |
| Weight | 0.006 lbs [2.72 g] |
| Body Material and Plating | Passivated Stainless Steel |

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Configuration

Design Fixed
 Package Style Connectorized Module

Connectors

| Description | Connector 1 | Connector 2 |
|----------------------------|----------------------------|------------------------|
| Type | SMP Male | SMP Female |
| Connection Method | Full Detent | |
| Contact Material & Plating | Phosphor Bronze, Gold | Beryllium Copper, Gold |
| Contact Plating Spec. | 4 μ-in min. | 4 μ-in min. |
| Dielectric Type | Teflon | Teflon |
| Body Material & Plating | Passivated Stainless Steel | Beryllium Copper, Gold |
| Body Plating Spec. | | 4 μ-in min. |

Environmental Specifications

Temperature


Operating Range -50 to +80 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data




30 dB Fixed Attenuator SMP Male Full Detent to SMP Female Up to 10 GHz Rated to 2 Watts with Passivated Stainless Steel Body from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [30 dB Fixed Attenuator SMP Male Full Detent to SMP Female Up to 10 GHz Rated to 2 Watts with Passivated Stainless Steel Body SA10P2W-30](#)

URL: <https://www.fairviewmicrowave.com/30db-fixed-attenuator-smp-male-smp-female-2-watts-sa10p2w-30-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





| P/N | ATTEN. |
|------------|--------|
| SA10P2W-01 | 1 dB |
| SA10P2W-02 | 2 dB |
| SA10P2W-03 | 3 dB |
| SA10P2W-04 | 4 dB |
| SA10P2W-05 | 5 dB |
| SA10P2W-06 | 6 dB |
| SA10P2W-10 | 10 dB |
| SA10P2W-15 | 15 dB |
| SA10P2W-20 | 20 dB |
| SA10P2W-30 | 30 dB |

| GENERAL TOLERANCES | |
|--------------------|--------------|
| 0.000-0.197 | ± 0.0020 |
| 0.197-0.394 | ± 0.0027 |
| 0.394-0.787 | ± 0.0039 |
| 0.787-1.181 | ± 0.0059 |
| >1.181 | ± 0.078 |

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

| | | | | | |
|---|--------|---|-------|--------------------|-------------|
| FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM | | NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm]. | | | |
| TITLE 30 dB Fixed Attenuator SMP Male Full Detent to SMP Female Up to 10 GHz Rated to 2 Watts with Passivated Stainless Steel Body | | DWG NO SA10P2W | | CAGE CODE 3FKR5 | |
| CAD FILE | 032216 | SHEET | SCALE | N/A | SIZE A 3045 |