

FMWSP1011 DATA SHEET

WR-137 Waveguide Pressurizing Section 4.25 Inch Length With UG-344/U Round Cover Flange from 5.85 GHz to 8.2 GHz

The FMWSP1011 is a pressurizing section for WR-137 waveguides with UG-344/U Round Cover flanges. The pressure section has a pressure gauge to monitor the internal pressure. The pressure gauge will read up to 15 PSI. It also has a pressure inlet valve which is a Schrader 1/8-27 NPTF with protective metal cap. The FMWSP1011 is part of a family of pressure inlets with pressure gauges. Used with Fairview Microwave's gasket kits it allows for waveguide systems to be pressurized with air or other gasses. These are quality built units with VSWR of 1.08:1 or less.



Description	Min	Тур	Max	Units
Frequency Range	5.85		8.2	GHz
VSWR		1.07:1		

^{*} Values at 25°C, sea level

Mechanical Specifications

Waveguide Size WR-137 Waveguide Design Standard

Section Length 4.25 in [107.95 mm]

Flange 1

Flange Type Round Cover Flange Designation UG-344/U

Waveguide

Interface WR-137 Material Bronze

Flange 2

Flange Type Round Cover Flange Designation UG-344/U

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Values at 25 °C, sea level



Features:


- Pressurizing Waveguide Section
- 0-15 PSI Pressure Gauge
- 5.85 GHz to 8.2 GHz Frequency Range
- UG-344/U Round Cover Flange
- Waveguide Body made of Bronze with Brass Flanges
- Low VSWR

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com



Typical Performance Data



WR-137 Waveguide Pressurizing Section 4.25 Inch Length With UG-344/U Round Cover Flange from 5.85 GHz to 8.2 GHz from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: WR-137 Waveguide Pressurizing Section 4.25 Inch Length With UG-344/U Round Cover Flange from 5.85 GHz to 8.2 GHz FMWSP1011

URL: https://www.fairviewmicrowave.com/wr-137-waveguide-section-straight-ug344-round-standard-fmwsp1011-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
WR-137 Waveguide Pressurizing Section 4.25 Inch Length With UG-344/U Round Cover Flange from 5.85 GHz to 8.2 GHz	FMWSP1011			CAGE CODE 3FKR5			
	CAD FILE 062117	SHEET 1 OF 1	SCAL	E N/A	SIZE A	9999	