

Times Microwave LMR-600-75-DB 75 Ohm Low Loss Flexible Coax Cable PE Jacket

LMR-600-75-DB

Configuration

- Low Loss Flexible Cable
- 1 Shield(s)

Features

- Max Operating Frequency of 2.5 GHz
- Phase Velocity 87% VoP
- Max Operating Temperature +85°C

Applications

- Laboratory Applications
- General Purpose RF Interconnect

Description

LMR-600-75-DB low-loss coax cable from Fairview Microwave is only one of many radio frequency coaxial cable types specifically stocked to be ready for same business day shipment. Fairview Microwave's LMR-600-75-DB coax cable is manufactured in a flexible design and has a 75 Ohm impedance. This flexible 75 Ohm coax cable is constructed with a polyethylene jacket of 0.59-inch diameter. Our RF coaxial cable is ideal for laboratory applications and general purpose RF interconnect applications.

Fairview Microwave's LMR-600-75-DB flexible coax cable with a polyethylene jacket is rated for a maximum operating frequency of 2.5 GHz. Our low-loss RF coaxial cable has a conductor made of copper. Our coax cable has a typical loss/attenuation of 0.4, 0.5, 0.9, 1.1, 1.3, 1.6, 2.3, 3.1, 3.7, and 4.2 dB/100ft at frequency of 30 MHz, 50 MHz, 150 MHz, 220 MHz, 450 MHz, 900 MHz, 1.5 GHz, 1.8 GHz, 2 GHz, and 2.5 GHz respectively.

The LMR-600-75-DB coax cable with PTFE dielectric can operate at temperatures ranging from -40 to 85 degrees C. Additional specifications for this LMR-600-75-DB RF coaxial cable are on our downloadable PDF datasheet above. This low-loss RF cable has a repeat minimum bend radius of 1 inch.

LMR-600-75-DB low-loss RF cable is part of more than one million RF, microwave, and millimeter wave parts in stock at Fairview Microwave. This LMR-600-75-DB coax cable is ready to buy and can be shipped worldwide. Fairview Microwave also maintains a wide selection of other radio frequency coaxial cable types that ship the same business day from our warehouse in the United States, as with the rest of our other RF/microwave and millimeter wave components.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		2.5	GHz
Impedance		75		Ohms
Velocity of Propagation		87		%
Inner Conductor DC Resistance			1.39	Ohms/1000ft
Outer Conductor DC Resistance			1.2	Ohms/1000ft

Times Microwave LMR-600-75-DB 75 Ohm
 Low Loss Flexible Coax Cable PE Jacket

LMR-600-75-DB
Performance by Frequency Band

Description	F1	F2	F3	F4	F5	Units
Frequency	30	50	150	220	300	MHz
Attenuation, Typ	0.4	0.5	0.9	1.1	1.3	dB/100ft
	1.31	1.64	2.95	3.61	4.27	dB/100m

Description	F6	F7	F8	F9	F10	Units
Frequency	0.45	0.9	1.5	2	2.5	GHz
Attenuation, Typ	1.6	2.3	3.1	3.7	4.2	dB/100ft
	5.25	7.55	10.17	12.14	13.78	dB/100m

Mechanical Specifications

Diameter	0.59 in [14.99 mm]
Weight	0.035 lbs/ft [0.05 kg/m]
Min. Bend Radius (Repeated)	1 in [25.4 mm]

Construction Specifications

Description	Material and Plating	Diameter
Inner Conductor	Copper Clad Aluminum, Strand	0.108 in [2.74 mm]
Dielectric	PTFE	0.455 in [11.56 mm]
First Shield	Aluminum Tape	
Outer Conductor		0 in [0 mm]
Jacket	PE	0.59 in [14.99 mm]

Environmental Specifications

Temperature	
Operating Range	-40 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Times Microwave LMR-600-75-DB 75 Ohm Low Loss Flexible Coax Cable PE Jacket

LMR-600-75-DB

Times Microwave LMR-600-75-DB 75 Ohm Low Loss Flexible Coax Cable PE Jacket from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Times Microwave LMR-600-75-DB 75 Ohm Low Loss Flexible Coax Cable PE Jacket LMR-600-75-DB](#)

URL: <https://www.fairviewmicrowave.com/75-ohm-lmr60075db-low-loss-flexible-coax-cable-pe-jacket-lmr-600-75-db-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

LMR-600-75-DB CAD Drawing

Times Microwave LMR-600-75-DB 75 Ohm Low Loss Flexible Coax Cable PE Jacket

