

SMA F'S POWER DIVIDER 2-4 GHZ 4 WAY

MP8426-4

SPECIFICATIONS

ELECTRICAL


FREQUENCY: 2-4 GHZ
 IMPEDANCE: 50 OHMS
 INPUT VSWR: 1.3:1 TYP
 OUTPUT VSWR: 1.2:1 TYP
 AMPLITUDE BALANCE: ± 0.30 dB
 PHASE BALANCE: $\pm 3^\circ$
 INSERTION LOSS: 0.60 dB
 POWER HANDLING : 30 WATTS
 ISOLATION: 20 DB

MECHANICAL


MATERIAL CONNECTORS: PASSIVATED STAINLESS STEEL
 MATERIAL CONTACTS: Au PLATED BeCu

OPERATING TEMPERATURE: -55°C TO +85°C

ROHS COMPLIANT



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA F'S POWER DIVIDER 2-4 GHZ 4 WAY

SIZE A	CAGE CODE 3FKR5	DWG NO MP8426-4	REV A
SCALE		SHEET	