

**10 dB Fixed Attenuator TNC Male To TNC Female Up To 3 GHz Rated To 1 Watt With Brass Tri-Metal Body**

Fairview Microwave carries a broad selection of fixed attenuators with a wide range of attenuation levels, frequency ranges, and power dissipation ranges. Also known as RF pads, RF microwave attenuators lower the amplitude of a signal (or attenuate) a known amount. These attenuator pads can be used in a wide variety of applications including reducing a signal level to protect measurement equipment or other circuitry, extending the range of power meters and amplifiers, and impedance matching circuits by reducing the VSWR seen by adjacent components. RF attenuators can prevent signal overload in amplifiers, receivers and detectors, adjusting the signal level to a range that is optimal.

Few RF components are as commonly used as fixed coaxial attenuators, and Fairview Microwave carries one of the largest in-stock selections and ships them same day. The SA3T-10 is a 10 dB Fixed Attenuator that operates from DC to 3 GHz and is rated to 1 Watt. The versatile coaxial package uses TNC male to TNC female connectors and is also REACH and RoHS compliant.



**Features:**

- DC to 3 GHz Frequency Range
- Attenuation 10 dB
- Max Power 1 Watt (CW)
- VSWR < 1.25:1

**Applications:**

- Instrumentation
- Precision measurements
- Prototyping and characterization
- Production systems

**Electrical Specifications**

Description	Min	Typ	Max	Units
Frequency Range	DC		3	GHz
Impedance		50		Ohms
Nominal Attenuation		10		dB
VSWR			1.25:1	
Input Power, CW			1	Watts
Input Power, Peak for 25 µsec.			100	Watts

**Electrical Specification Notes:**

Power coefficient of 0.001 dB/W (change in attenuation with increase in power)

Temperature coefficient of 0.001 dB/°C max., 0.0003 dB/°C typ.

**Mechanical Specifications**

**Size**

Length	2.08 in [52.83 mm]
Width/Diameter	0.63 in [16 mm]
Weight	0.0818 lbs [37.1 g]
Body Material and Plating	Brass, Tri-Metal

**Configuration**

Design	Fixed
Package Style	Connectorized Module

Fairview Microwave  
 1130 Junction Dr. #100  
 Allen, TX 75013  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

**Connectors**

Description	Connector 1	Connector 2
Type	TNC Male	TNC Female
Contact Material & Plating	Phosphor Bronze, Gold	Phosphor Bronze, Gold
Contact Plating Spec.	10 μ-in.	10 μ-in.
Dielectric Type	Teflon	Teflon
Body Material & Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Spec.	100 μ-in.	100 μ-in.

**Environmental Specifications**

**Temperature**

Operating Range -50 to +80 deg C

**Compliance Certifications** (visit [www.FairviewMicrowave.com](http://www.FairviewMicrowave.com) for current document)

RoHS Compliant Yes  
 REACH Compliant 12/17/2015

**Plotted and Other Data**


Notes:

10 dB Fixed Attenuator TNC Male To TNC Female Up To 3 GHz Rated To 1 Watt With Brass Tri-Metal Body from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [10 dB Fixed Attenuator TNC Male To TNC Female Up To 3 GHz Rated To 1 Watt With Brass Tri-Metal Body SA3T-10](#)

URL: <https://www.fairviewmicrowave.com/10db-fixed-attenuator-tnc-male-tnc-female-1-watt-sa3t-10-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



P/N	ATTEN.
SA3T-03	3 dB
SA3T-06	6 dB
SA3T-10	10 dB
SA3T-15	15 dB
SA3T-20	20 dB

STANDARD TOLERANCES	
.X	±0.03
.XX	±0.010
.XXX	±0.005

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MW  
 SA3T-XX

↑  
 LABEL

<b>FAIRVIEW MICROWAVE INC.</b> ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE 10 dB Fixed Attenuator TNC Male To TNC Female Up To 3 GHz Rated To 1 Watt With Brass Tri-Metal Body		DWG NO SA3T		CAGE CODE 3FKR5	
CAD FILE	031616	SHEET	SCALE	N/A	SIZE A 3045