

VARIABLE ATTENUATOR 2-4 GHZ 40dB SMA F'S

SA4073


SPECIFICATIONS

ELECTRICAL:


FREQUENCY: 2-4 GHZ
 VSWR 1.6:1 MAX
 POWER CW: 5 WATTS
 INSERTION LOSS: 0.5 dB MAX
 IMPEDANCE: 50 OHMS
 ATTENUATION RANGE: 0-40 dB

MATERIAL CONNECTORS: STAINLESS STEEL
 MATERIAL CONTACTS: Au PLATED BeCu
 MATERIAL BODY: ALUMINUM

***UNITS USE MULTI-TURN NON TRANSLATING SHAFTS,
 FULL ATTENUATION IS REACHED IN LESS THAN 25 TURNS



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

**VARIABLE ATTENUATOR 2-4 GHZ
 40dB SMA F'S**

SIZE CAGE CODE DWG NO

A

3FKR5

SA4073

REV

--

SCALE

SHEET