

SA6H-16 DATA SHEET

16 dB Fixed Attenuator SMA Male To SMA Female Up To 6 GHz Rated To 2 Watts With Passivated Stainless Steel Body

Fairview Microwave carries a broad selection of fixed attenuators with a wide range of attenuation levels, frequency ranges, and power dissipation ranges. Also known as RF pads, RF microwave attenuators lower the amplitude of a signal (or attenuate) a known amount. These attenuator pads can be used in a wide variety of applications including reducing a signal level to protect measurement equipment or other circuitry, extending the range of power meters and amplifiers, and impedance matching circuits by reducing the VSWR seen by adjacent components. RF attenuators can prevent signal overload in amplifiers, receivers and detectors, adjusting the signal level to a range that is optimal.

Few RF components are as commonly used as fixed coaxial attenuators, and Fairview Microwave carries one of the largest in-stock selections and ships them same day. The SA6H-16 is a 16 dB Fixed Attenuator that operates from DC to 6 GHz and is rated to 2 Watts. The versatile coaxial package uses SMA male to SMA female connectors and is also REACH and RoHS compliant.

Electrical Specifications

| Description | Min | Тур | Мах | Units |
|--|-------------|-----|--------|-------|
| Frequency Range | DC | | 6 | GHz |
| Impedance | | 50 | | Ohms |
| Nominal Attenuation | | 16 | | dB |
| Attenuation Accuracy | | | ±0.75 | dB |
| VSWR | | | 1.35:1 | |
| Input Power, CW derated linearly to 0.2 | W at +125°C | | 2 | Watts |
| Input Power, Peak 5µs pulse, 0.01% duty | / cycle | | 200 | Watts |
| | | | | - |



Features:

- DC to 6 GHz Frequency Range
- Attenuation 16±0.75 dB
- Max Power 2 Watts (CW)
- VSWR < 1.35:1

Applications:

- Instrumentation
- Precision measurements
- Prototyping and characterization
- Production systems

Mechanical Specifications

Size Length Width/Diameter Weight Body Material and Plating

Configuration

Design Package Style 0.86 in [21.84 mm] 0.312 in [7.92 mm] 0.012 lbs [5.44 g] Passivated Stainless Steel

Fixed Connectorized Module

> Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Connectors

| Description Connector 1 | |
|----------------------------|--|
| SMA Male | SMA Female |
| Beryllium Copper, Gold | Beryllium Copper, Gold |
| Teflon | Teflon |
| 5/16 inch | 5/16 inch |
| 8 in-lbs [0.9 Nm] | |
| Passivated Stainless Steel | Passivated Stainless Steel |
| | SMA Male Beryllium Copper, Gold Teflon 5/16 inch 8 in-lbs [0.9 Nm] |

Environmental Specifications Temperature

| Temperature | |
|-----------------|--|
| Operating Range | |

-65 to +125 deg C


Compliance Certifications (visit www.FairviewMicrowave.com for current document)

| RoHS Compliant | Yes | |
|-----------------|------------|--|
| REACH Compliant | 12/17/2015 | |

Plotted and Other Data

Notes:

Typical Performance Data








16 dB Fixed Attenuator SMA Male To SMA Female Up To 6 GHz Rated To 2 Watts With Passivated Stainless Steel Body from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 16 dB Fixed Attenuator SMA Male To SMA Female Up To 6 GHz Rated To 2 Watts With Passivated Stainless Steel Body SA6H-16


URL: http://www.fairviewmicrowave.com/16db-fixed-attenuator-sma-male-sma-female-2-watts-sa6h-16-p.aspx



1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







| <u>STANDA</u> | RD TOLERANCES |
|---------------|---------------|
| .x | ±0.03 |
| .xx | ± 0.010 |
| .xxx | ±0.005 |
| | |

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

| FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM | NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm]. | | | | | |
|--|---|-------|-------|-----------------|--------|------|
| TITLE 16 dB Fixed Attenuator SMA Male To SMA Female Up To 6 GHz Rated To 2 Watts With Passivated Stainless Steel Body | DWG NO SA6H | | | CAGE CODE 3FKR5 | | |
| | CAD FILE 031716 | SHEET | SCALE | N/A | SIZE A | 3045 |

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689