

ATTENUATOR 150W N M/F 8.5GHZ UNIDIRECTIONAL

SA8N005-XX

SPECIFICATIONS

ELECTRICAL:

FREQUENCY: 0-8.5 GHZ
 IMPEDANCE: 50 OHMS
 VSWR @ 4 GHZ: 1.2 MAX
 VSWR @ 8.5 GHZ: 1.35 MAX
 POWER (AVG) 150 WATTS @ 25° C
 DERATED LINEARLY TO 10% @ 125° C
 POWER (PEAK) 2,500 WATTS
 5 μs PULSE WIDTH WITH 1% DUTY CYCLE

ATTENUATION ACCURACY:

3-30 dB +/- .75 dB
 40 dB +/- 1.0 dB

INTERFACE: MIL-STD-348
 CONNECTORS: STAINLESS STEEL
 FEMALE CONTACT: Au PLATED BeCu
 Au PLATING MIL-G-45204


ENVIRONMENTAL:

TEMP: -55 C TO +125 C

ROHS COMPLIANT

UNIDIRECTIONAL

**MALE IS INPUT FEMALE IS OUTPUT



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

**ATTENUATOR 150W N M/F 8.5GHZ
UNIDIRECTIONAL**

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SA8N005-XX	A
SCALE		SHEET	

ALL DIMENSIONS IN inches(mm) Typical