

TNC-M .141" SEMIRIGID CLAMP

SC4270

SPECIFICATIONS

ELECTRICAL:


FREQUENCY: 0-11 GHZ
VSWR 1.3:1 MAX
IMPEDANCE: 50 OHMS

MECHANICAL:

MATERIAL BODY: NICKLE PLATED BRASS
CENTER CONTACT: BRASS
CONTACT PLATING: Au MIL-G-45204
SOLDER FERRULE: Au PLATED
INSULATOR: TEFLON
INTERFACE: MIL-STD-348B
ROHS COMPLIANT
OP. TEMP RANGE: -55°C- +155°C

ASSEMBLY INSTRUCTIONS:

TRIM CABLE AS SHOWN;
SLIDE BACKNUT, WASHER, GASKET, CLAMP ON CABLE;
SOLDER FERRULE TO JACKET;
SOLDER CONTACT TO CENTER CONDUCTOR
INSERT CABLE ASSEMBLY INTO JACKET & TIGHTEN BACKNUT



Ø.5"

1.09"



.109"
.219"

STRIPPING DIMENSIONS

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

TNC-M .141" SEMIRIGID CLAMP

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SC4270	--

SCALE

SHEET