

SC4821 DATA SHEET

HN Male Connector Clamp/Solder Attachment For RG214, RG213, RG393, RG8, RG225, RG215, RG9 Cable

HN male connector with clamp/solder attachment for RG214, RG213, RG393, RG8, RG225, RG215 and RG9, part number SC4821, from Fairview Microwave is in-stock and ships same day. This HN male connector operates up to a maximum frequency of 6 GHz and offers good VSWR of 1.5:1.

Fairview's HN male connector SC4821 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		6	GHz
VSWR			1.5:1	
Operating Voltage (AC)			1,500	Vrms
•				

Mechanical Specifications

Size Length Width/Dia.

Weight

2.03 in [51.56 mm] 0.866 in [22.00 mm]

0.1675 lbs [75.98 g]

Material Specifications

Description Material		Plating	
Contact	Brass	Gold 30 µin minimum	
Insulation	PTFE		
Body	Brass	Nickel 100 µin minimum	
Coupling Nut Brass		Nickel 100 µin minimum	

Mechanical Specification Notes:

When attaching the connector to the cable use a clamp torque value of 60 to 65 in-lbs [6.78 to 7.34 Nm]



Configuration:

- · HN Male Connector
- MIL-STD-348A
- 50 Ohms
- Straight Body Geometry
- RG214, RG213, RG393, RG8, RG225, RG215, RG9 Interface Type
- Clamp/Solder Attachment

Features:

- Operating Frequency of 6 GHz Max.
- Good VSWR of 1.5:1
- · Gold Plated Brass Contact
- 30 µin minimum contact plating

Applications:

- General Purpose Test
- Custom Cable Assemblies

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Environmental Specifications

Temperature

Operating Range

Compliance Certifications (see product page for current document)


Plotted and Other Data

Notes:


Assembly Instruction

ASSEMBLY PROCEDURES


-65 to +165 deg C



2. SLIDE BRAID CLAMP (4) OVER BRAID & SEAT AGAINST CABLE. FORM BRAID OVER CLAMP NUT. TRIM BRAID BACK TO SHOULDER. CUT DIELECTRIC & CENTER CONDUCTOR TO DIMENSION SHOWN. DO NOT NICK CENTER CONDUCTOR.



3. SOLDER CONTACT 5 TO CENTER CONDUCTOR. REMOVE EXCESS SOLDER. DO NOT OVER HEAT DIELECTRIC. INSERT CABLE ASSEMBLY INTO BODY 6 & TIGHTEN.



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





HN Male Connector Clamp/Solder Attachment For RG214, RG213, RG393, RG8, RG225, RG215, RG9 Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: HN Male Connector Clamp/Solder Attachment For RG214, RG213, RG393, RG8, RG225, RG215, RG9 Cable SC4821

URL: https://www.fairviewmicrowave.com/hn-male-standard-rg8-rg213-rg225-rg393-connector-sc4821-p.aspx





2.230 56.64 .748 866 [19] 21.99 5/8 FLATS 1/2 FLATS (3) (4) 6 2 **STANDARD TOLERANCES** .X ±0.2 .XX ±0.01 .XXX ± 0.005 *STANDARD TOLERANCES APPLY

FAIRVIEW MICROWAVE INC. NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm]. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM DWG NO CAGE CODE SC4821 3FKR5 HN Male Connector Clamp/Solder Attachment For RG214, RG213, RG393, RG8, RG225, RG215, RG9 Cable CAD FILE 091517 SHEET 1 OF 1 SCALE N/A SIZE A 7361

ONLY TO DIMENSIONS IN INCHES