

TNC-M RG55, RG58 GRIP ASSEMBLY

SC4267

SPECIFICATIONS

ELECTRICAL:


FREQUENCY: 0-11 GHZ
 VSWR 1.3:1 MAX
 IMPEDANCE: 50 OHMS

MECHANICAL:


MATERIAL BODY: NICKLE PLATED BRASS
 CENTER CONTACT: BRASS
 CONTACT PLATING: Si QQ-S-365
 INSULATOR: TEFLON
 CAPTIVATED CONTACT
 INTERFACE: MIL-STD-348B
 ROHS COMPLIANT
 OP. TEMP RANGE: -55°C- +155°C

ASSEMBLY INSTRUCTIONS:

SLIDE BACKNUT ONTO CABLE
 TRIM CABLE AS SHOWN
 SLIT CABLE, 2 PLACES AS SHOWN, 180° APART
 SLIDE PIN ASSEMBLY UNDER BRAID
 SOLDER PIN ASSEMBLY TO CENTER CONDUCTOR
 INSERT ASSEMBLY INTO BODY
 TIGHTEN BY HOLDING NUT, TURNING BODY



SLIT, X2



STRIPPING DIMENSIONS

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

TNC-M RG55, RG58 GRIP ASSEMBLY

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SC4267	--
SCALE	SHEET		