

**N Male Connector Crimp/Solder Attachment For  
 RG55, RG142, RG223, RG400 Cable**

Type N male connector with crimp/solder attachment for RG55, RG142, RG223 and RG400, part number SC9107, from Fairview Microwave is in-stock and ships same day. This type N male connector operates up to a maximum frequency of 11 GHz and offers good VSWR of 1.45:1.

Fairview's type N male connector SC9107 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

**Electrical Specifications**

Description	Min	Typ	Max	Units
Frequency Range	DC		11	GHz
VSWR			1.45:1	
Operating Voltage (AC)			1,000	Vrms
DWV (AC)			1,500	Vrms
Insulation Resistance	5,000			MOhms

**Mechanical Specifications**

<b>Size</b>	
Length	1.51 in [38.35 mm]
Width/Dia.	0.8 in [20.32 mm]
Weight	0.0815 lbs [36.97 g]
Mating Cycles	500 Cycles

**Material Specifications**

Description	Material	Plating
Contact	Brass	Gold ASTM B488
Insulation	PTFE	
Body	Brass	Nickel QQ-N-290
Coupling Nut	Brass	Nickel QQ-N-290
Gasket	Silicone Rubber	

**Environmental Specifications**

<b>Temperature</b>	
Operating Range	-65 to +165 deg C
Shock	MIL-STD-202, METH. 213 COND I



**Configuration:**

- N Male Connector
- MIL-STD-348
- 50 Ohms
- Straight Body Geometry
- RG55, RG142, RG223, RG400 Interface Type
- Crimp/Solder Attachment

**Features:**

- Operating Frequency of 11 GHz Max.
- Good VSWR of 1.45:1
- Gold Plated Brass Contact
- Contact plating according to ASTM B488

**Applications:**

- General Purpose Test
- Custom Cable Assemblies

Fairview Microwave  
 1130 Junction Dr. #100  
 Allen, TX 75013  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

Vibration	MIL-STD-202, METH. 204 COND D
Altitude	MIL-STD-202, METH. 105 COND C
Thermal Shock	MIL-STD-202, METH. 107 COND B

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**


Notes:

N Male Connector Crimp/Solder Attachment For RG55, RG142, RG223, RG400 Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [N Male Connector Crimp/Solder Attachment For RG55, RG142, RG223, RG400 Cable SC9107](#)

URL: <https://www.fairviewmicrowave.com/n-male-standard-rg55-rg142-rg223-connector-sc9107-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



STANDARD TOLERANCES	
.X	±0.2
.XX	±0.1
.XXX	±0.05

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

<b>FAIRVIEW MICROWAVE INC.</b> ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE N Male Connector Crimp/Solder Attachment For RG55, RG142, RG223, RG400 Cable		DWG NO SC9107		CAGE CODE 3FKR5	
CAD FILE	021617	SHEET	SCALE	N/A	SIZE A 2233