

SMA-M RG8X LMR240 CRIMP RA

SC7034

SPECIFICATIONS



ELECTRICAL:

FREQUENCY: 0-6 GHZ
 VSWR 1.3:1 MAX
 IMPEDANCE: 50 OHMS
 OP. TEMP RANGE: -55°C- +85°C

MECHANICAL:

MATERIAL BODY: PASS. STAINLESS STEEL
 CENTER CONTACT: BRASS
 CONTACT PLATING: Au PER MIL-G-45204
 INSULATOR: TEFLON
 INTERFACE: MIL-STD-348A

ROHS COMPLIANT



STRIPPING DIMENSIONS

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA-M RG8X LMR240 CRIMP RA

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SC7034	--
SCALE		SHEET	

ALL DIMENSIONS IN inches(MM) Typical