## N-M CLAMP RG55, RG58

SC9302

## **SPECIFICATIONS**

**ELECTRICAL**:

FREQUENCY: 0-11 GHZ

**VSWR 1.3:1 MAX** 

IMPEDANCE: 50 OHMS

MECHANICAL:

MATERIAL BODY: NICKLE PLATED BRASS

**CENTER CONTACT: BRASS** 

CONTACT PLATING: Si QQ-S-365

INSULATOR: TEFLON

INTERFACE: MIL-STD-348B

**ROHS COMPLIANT** 

OP. TEMP RANGE: -55°C- +155°C

**ASSEMBLY INSTRUCTIONS:** 

TRIM CABLE TO OVERALL LENGTH AS SHOWN;

SLIDE BACKNUT, WASHER, GASKET, CLAMP ON CABLE:


COMB BRAID WIRES OUT, FOLD BACK, TRIM FLUSH W CLAMP;

TRIM DIELECTRIC & CENTER PIN AS SHOWN:

ASSEMBLE REAR BUSHING:

SOLDER CONTACT ONTO CENTER CONDUCTOR,

INSERT ASSEMBLY INTO BODY, TIGHTEN NUT



STRIPPING DIMENSIONS

## FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

N-M CLAMP RG55, RG58

SIZE CAGE CODE DWG NO A 3FKR5 SC9302 ---

4