

SPECIFICATIONS

N-M CRIMP RG8, RG213, RG11

ELECTRICAL:

FREQUENCY: 0-12 GHZ
 VSWR 1.3:1 MAX
 IMPEDANCE: 50 OHMS


MECHANICAL:

MATERIAL BODY: NICKLE PLATED BRASS
 CENTER CONTACT: BRASS
 CAPTIVATED CONTACT
 CONTACT PLATING: Au MIL-G-45204
 INSULATOR: TEFLON
 INTERFACE: MIL-STD-348B
 ROHS COMPLIANT
 OP. TEMP RANGE: -55°C- +155°C

ASSEMBLY INSTRUCTIONS:

TRIM CABLE AS SHOWN;
 SOLDER CONTACT ONTO CENTER CONDUCTOR,
 CHECK THAT BACK OF CONTACT IS FLUSH WITH DIELECTRIC;
 FLARE BRAID SLIGHTLY BY ROTATING;
 INSERT CABLE/CONTACT INTO REAR OF BODY;
 ALL BRAID WIRES OUTSIDE OF CRIMP TAIL;
 PUSH CABLE IN UNTIL CONTACT SNAPS INTO INSULATOR;
 TRIM EXCESS BRAID WIRES;
 SLIDE SLEEVE FORWARD, CRIMP

SC9103



STRIPPING DIMENSIONS

				FAIRVIEW MICROWAVE INC.			
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
				TITLE			
				N-M CRIMP RG8, RG213, RG11			
SIZE		CAGE CODE		DWG NO		REV	
A		3FKR5		SC9103			
SCALE				SHEET			