

N-M/RA CRIMP RG9 RG214 RG393

SC9106

SPECIFICATIONS

ELECTRICAL:

FREQUENCY: 0-11 GHZ
 IMPEDANCE: 50 OHMS
 WORKING VOLTAGE: 1000 VOLTS MAX
 VSWR: 1.35 MAX



MECHANICAL:

MATERIAL BODY: NICKEL PLATED BRASS 100μ"
 CENTER CONTACT: Au PLATED BRASS 30μ" MIN
 DIELECTRIC: TEFLON
 INTERFACE: MIL-STD-348A
 OP. TEMP RANGE: -65°C- +165°C


INNER: SOLDER OUTER: CRIMP

HEX CRIMP TOOLS REQUIRED: 10.9(.429")

ROHS COMPLIANT



STRIPPING DIMENSION



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

N-M/RA CRIMP RG9 RG214 RG393

| | | | |
|----------|--------------|---------------|-----|
| SIZE | CAGE CODE | DWG NO | REV |
| A | 3FKR5 | SC9106 | -- |
| SCALE | | SHEET | |

ALL DIMENSIONS IN inches(mm) Typical