

## SSMC Plug to SSMC Plug Cable FM-SR405FL Coax in 6 Inch

The SSMC plug to SSMC plug 6 inch cable using FM-SR405FL coax, part number SCA29086-06, from Fairview Microwave is in-stock and ships same day. This Fairview SSMC to SSMC cable assembly has a plug to plug gender configuration with 50 ohm formable FM-SR405FL coax. Fairview Microwave's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. The SCA29086-06 SSMC plug to SSMC plug cable assembly operates to 6 GHz. The SSMC male to SSMC male 6 inch cable using RG405 type .086 coax, part number SCA29086-06, from Fairview Microwave is in-stock and ships same day. This Fairview SSMC to SSMC cable assembly has a male to male gender configuration with 50 ohm formable FM-SR405FL coax. Fairview Microwave's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. The SCA29086-06 SSMC male to SSMC male cable assembly operates to 6 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		6	GHz
VSWR			1.35:1	

### Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	3	6			GHz
Insertion Loss (Typ.)	0.12	0.18	0.28			dB

#### Electrical Specification Notes:

Insertion loss does not include the loss of the connectors.

Insertion loss is estimated as  $0.05 \times \sqrt{f(\text{GHz})}$  dB per connector.

### Mechanical Specifications

#### Cable Assembly

Length\* 6 in [152.4 mm]  
 Weight 0.014 lbs [6.35 g]

#### Cable

Cable Type FM-SR405FL  
 Impedance 50 Ohms



### Configuration:

- SSMC Plug
- SSMC Plug
- FM-SR405FL


### Features:

- Max Frequency 6 GHz
- Max Frequency 6 GHz

### Applications:

- General Purpose
- Laboratory Use
- General Purpose
- Laboratory Use

### Cable Diagram:



Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Outer Conductor Material and Plating	Tinned Copper Braid
Outer Conductor Diameter	0.086 in [2.18 mm]

**Connectors**

Description	Connector 1	Connector 2
Type	SSMC Plug	SSMC Plug
Configuration	Straight	Straight
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Dielectric Type	PTFE	PTFE
Body Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Coupling Nut Material & Plating	Brass, Gold	Brass, Gold
Hex Size	1/4 inch	1/4 inch

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

**How to Order**

Part Number Configuration:

**SCA29086 - xx uu**

cm = Centimeters  
<blank> = Inches  
Length


Example: SCA29086-12 = 12 inches long cable  
SCA29086-100cm = 100 cm long cable

SSMC Plug to SSMC Plug Cable FM-SR405FL Coax in 6 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [SSMC Plug to SSMC Plug Cable FM-SR405FL Coax in 6 Inch SCA29086-06](#)

URL: <https://www.fairviewmicrowave.com/ssmc-plug-ssmc-plug-cable-coax-sca29086-06-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



STANDARD TOLERANCES	
.X	±0.2
.XX	±0.1
.XXX	±0.05

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

**FAIRVIEW MICROWAVE INC.**  
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:  
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
3. DIMENSIONS ARE IN INCHES [mm].

TITLE SSMC Plug to SSMC Plug Cable FM-SR405FL Coax in 6 Inch	DWG NO SCA29086		CAGE CODE 3FKR5		
	CAD FILE 101816	SHEET	SCALE N/A	SIZE A	41742