

# N-M CLAMP RG8, RG9, RG11

SC9175

## SPECIFICATIONS

### ELECTRICAL:


FREQUENCY: 0-12 GHZ  
 VSWR 1.3:1 MAX  
 IMPEDANCE: 50 OHMS

### MECHANICAL:

MATERIAL BODY: NICKLE PLATED BRASSS  
 CENTER CONTACT: BRASS  
 CONTACT PLATING: Au MIL-G-45204  
 INSULATOR: TEFLON  
 CAPTIVATED CONTACT  
 INTERFACE: MIL-STD-348B  
 ROHS COMPLIANT  
 OP. TEMP RANGE: -55°C- +155°C

### ASSEMBLY INSTRUCTIONS:

TRIM CABLE TO OVERALL LENGTH AS SHOWN;  
 SLIDE BACKNUT, WASHER, GASKET, CLAMP ON CABLE;  
 COMB BRAID WIRES OUT, FOLD BACK, TRIM FLUSH W CLAMP;  
 TRIM DIELECTRIC & CENTER PIN AS SHOWN;  
 ASSEMBLE REAR BUSHING;  
 SOLDER CONTACT ONTO CENTER CONDUCTOR,  
 INSERT ASSEMBLY INTO BODY, TIGHTEN NUT



STRIPPING DIMENSIONS

				<b>FAIRVIEW MICROWAVE INC.</b>			
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
				TITLE			
				<b>N-M CLAMP RG8, RG9, RG11</b>			
SIZE		CAGE CODE		DWG NO		REV	
<b>A</b>		<b>3FKR5</b>		<b>SC9175</b>			
SCALE				SHEET			