

BNC/M - BNC/M FLEXIBLE CABLES 6GHZ LMR240

SCB15392-XX

SPECIFICATIONS

CABLE ASSEMBLY:
VSWR:1.2:1 @<6GHZ TYPICAL

RAW CABLE: LMR240
TYPICAL LOSS (EXCLUDING CONNECTORS)
@ 500MHZ: 0.056 DB/FT
@1GHZ: 0.081 DB/FT
@2GHZ: 0.12 DB/FT
@3GHZ: 0.14 DB/FT
OUTER SHIELD DIAMETER: .240"


CONNECTORS:
BNC: BRASS
CONTACTS Au PLATING
INTERFACE: MIL-STD-348A

OP TEMP: -55-110°C

XX" +/- .100"


PROTECTIVE HEAT SHRINK

BNC-M



BNC-M

MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

BNC/M - BNC/M FLEXIBLE CABLES 6GHZ LMR240

SIZE

A

CAGE CODE

3FKR5

DWG NO

SCB15392-XX

REV

--

SCALE

SHEET