

BNC/M - BNC/M FLEXIBLE CABLES 3GHZ RG174

SCB15307-XX


SPECIFICATIONS

CABLE ASSEMBLY:
VSWR:1.2:1 MAX @<3GHZ TYPICAL


RAW CABLE: TIMES MICROWAVE RG174
TYPICAL LOSS (EXCLUDING CONNECTORS)
@ 100MHZ: 0.08 DB/FT
@500MHZ: 0.19 DB/FT
@1GHZ: 0.28 DB/FT
@2GHZ:0.40 DB/FT
@3GHZ:0.49 DB/FT
OUTER SHIELD DIAMETER: .100"

CONNECTORS:
BNC: BRASS
CONTACTS Au PLATING
INTERFACE: MIL-STD-348A

OP TEMP: -55-110°C



MEASUREMENTS BELOW ARE TYPICAL 12in CABLE



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

BNC/M - BNC/M FLEXIBLE CABLES 3GHZ RG174

| | | | |
|------|-----------|-------------|-----|
| SIZE | CAGE CODE | DWG NO | REV |
| A | 3FKR5 | SCB15307-XX | -- |

SCALE

SHEET