

BNC/M - BNC/M FLEXIBLE CABLES 3GHZ RG316

SCB15311-XX

SPECIFICATIONS



CABLE ASSEMBLY:
VSWR: 1.2:1 @ < 3GHZ TYPICAL

RAW CABLE: RG316
TYPICAL LOSS (EXCLUDING CONNECTORS)
@100MHZ: 0.08DB/FT
@1GHZ: 0.26 DB/FT
@2GHZ: 0.37 DB/FT
@3Ghz 0.47 DB/FT
OUTER SHIELD DIAMETER: .195"

CONNECTORS:
BNC: BRASS
CONTACTS Au PLATING
INTERFACE: MIL-STD-348A

OP TEMP: -55-110°C

MEASUREMENTS BELOW ARE TYPICAL 12in CABLE



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.			
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
TITLE BNC/M - BNC/M FLEXIBLE CABLES 3GHZ RG316			
SIZE A	CAGE CODE 3FKR5	DWG NO SCB15311-XX	REV --
SCALE		SHEET	