



# Inner DC Block From 10 MHz to 18 GHz With TNC Connectors

## **Electrical Specifications**

Description	Min	Тур	Max	Units
Frequency Range	0.01		18	GHz
Impedance		50		Ohms
VSWR			1.35:1	
Insertion Loss			0.75	dB
Operating Voltage (DC)			200	Volts



### **Mechanical Specifications**

 Size
 2.07 in [52.58 mm]

 Width
 0.59 in [14.99 mm]

 Weight
 0.0218 lbs [9.89 g]

ConfigurationInner DC BlockDesignInner DC BlockPackage TypeConnectorized

Description	Connector 1	Connector 2		
Туре	TNC Male	TNC Female		
Connector Specification	MIL-STD-348	MIL-STD-348		

Compliance Certifications (visit www.FairviewMicrowave.com for current

document)

RoHS Compliant REACH Compliant


Yes

12/17/2014

#### **Plotted and Other Data**

Notes:

#### **Typical Performance Data**



Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Inner DC Block From 10 MHz to 18 GHz With TNC Connectors from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: Inner DC Block From 10 MHz to 18 GHz With TNC Connectors SD3470

URL: https://www.fairviewmicrowave.com/inner-dc-block-10-mhz-18-ghz-tnc-connectors-sd3470-p.aspx









STANDARD TOLERANCES
.X ±0.2
.XX ±0.1

.XX ±0.1 .XXX ±0.05

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  3. DIMENSIONS ARE IN INCHES [mm].					
Inner DC Block From 10 MHz to 18 GHz With TNC Connectors	DWG NO SD3470			CAGE CODE 3FKR5		
	CAD FILE 070716	SHEET	SCALE N/A		SIZE A	2233