

**Inner DC Block From 10 MHz to 26.5 GHz With 2.92mm Connectors**

**Electrical Specifications**

Description	Min	Typ	Max	Units
Frequency Range	0.01		26.5	GHz
Impedance		50		Ohms
VSWR			1.5:1	
Insertion Loss		0.5		dB
Operating Voltage (DC)			200	Volts



**Mechanical Specifications**

<b>Size</b>	
Length	0.855 in [21.72 mm]
Width	0.312 in [7.92 mm]
Weight	0.0138 lbs [6.26 g]

<b>Configuration</b>	
Design	Inner DC Block
Package Type	Connectorized

Description	Connector 1	Connector 2
Type	2.92mm Male	2.92mm Female
Inner Cond Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Outer Cond Material & Plating	Passivated Stainless Steel	Passivated Stainless Steel
Coupling Nut Material & Plating	Passivated Stainless Steel	
Hex Size	5/16 Inch	
Body Material & Plating	Passivated Stainless Steel	Passivated Stainless Steel

**Compliance Certifications** (visit [www.FairviewMicrowave.com](http://www.FairviewMicrowave.com) for current document)


RoHS Compliant	Yes
REACH Compliant	12/17/2014

**Plotted and Other Data**

Notes:

Fairview Microwave  
 1130 Junction Dr. #100  
 Allen, TX 75013  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

**Typical Performance Data**




Inner DC Block From 10 MHz to 26.5 GHz With 2.92mm Connectors from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [Inner DC Block From 10 MHz to 26.5 GHz With 2.92mm Connectors SD3473](https://www.fairviewmicrowave.com/inner-dc-block-10-mhz-26.5-ghz-2.92mm-connectors-sd3473-p.aspx)

URL: <https://www.fairviewmicrowave.com/inner-dc-block-10-mhz-26.5-ghz-2.92mm-connectors-sd3473-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



STANDARD TOLERANCES	
.X	±0.2
.XX	±0.1
.XXX	±0.05

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

<b>FAIRVIEW MICROWAVE INC.</b> ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE Inner DC Block From 10 MHz to 26.5 GHz With 2.92mm Connectors		DWG NO SD3473		CAGE CODE 3FKR5	
CAD FILE	070816	SHEET	SCALE	N/A	SIZE A 2233