

Isolator 2.92mm Female With 14 dB Isolation From 26.5 GHz to 40 GHz Rated to 5 Watts

The SFI2640 is a single junction isolator offering a forward power rating of 5 Watts CW and reverse power rating of 2 Watts CW over an operational frequency band of 26.5 to 40 GHz. This coaxial isolator uses 2.92mm female connectors on all ports and has a minimum of 14 dB isolation.

Fairview Microwave offers a wide variety of isolators to fit your needs. These are two-port devices that transmit microwave or radio frequency power in one direction only and block the signal in the opposite direction. They can be thought of as a diode for RF energy. Isolators are used to isolate equipment from the effects of conditions outside of the equipment. For instance they are used to prevent a microwave source being detuned by a mismatched load. Fairview Microwave's isolators feature excellent insertion loss, high isolation and reliability.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	26.5		40	GHz
Impedance		50		Ohms
Insertion Loss			1.75	dB
Isolation	14			dB
VSWR			1.5:1	
Forward Power, CW			5	Watts
Forward Power, Peak			30	Watts
Reverse Power, CW			2	Watts

Electrical Specification Notes:
 Values at 25°C, sea level.

Mechanical Specifications

Size	
Length	0.5 in [12.7 mm]
Width	0.7 in [17.78 mm]
Height	0.5 in [12.7 mm]
Weight	0.0463 lbs [21 g]

Configuration

Design	Single Junction
Direction	1 to 2
Package Style	Connectorized
Connector 1	2.92mm Female
Connector 2	2.92mm Female

Environmental Specifications

Temperature	
Operating Range	-20 to +65 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:



Features:


- 26.5 to 40 GHz Frequency Range
- Max Forward Power 5 Watts CW
- Max Reverse Power 2 Watts CW
- Insertion Loss < 1.75 dB
- VSWR < 1.5:1
- Isolation > 14 dB
- 2.92mm Female Connectors

Applications:

- Radar Systems
- Military
- Wireless Radio Systems
- Telecom Infrastructure
- Communication Systems
- R&D Labs
- Microwave Radio Systems

Fairview Microwave
 1130 Junction Dr. #100
 Allen, TX 75013
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Typical Performance Data




Isolator 2.92mm Female With 14 dB Isolation From 26.5 GHz to 40 GHz Rated to 5 Watts from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Isolator 2.92mm Female With 14 dB Isolation From 26.5 GHz to 40 GHz Rated to 5 Watts SFI2640](https://www.fairviewmicrowave.com/2.92mm-isolator-14-db-isolation-26.5-40-ghz-5-watts-sfi2640-p.aspx)

URL: <https://www.fairviewmicrowave.com/2.92mm-isolator-14-db-isolation-26.5-40-ghz-5-watts-sfi2640-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



STANDARD TOLERANCES	
.X	±0.2
.XX	±0.1
.XXX	±0.05

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE Isolator 2.92mm Female With 14 dB Isolation From 26.5 GHz to 40 GHz Rated to 5 Watts		DWG NO SFI2640	CAGE CODE 3FKR5		
CAD FILE	080816	SHEET	SCALE	N/A	SIZE A
					2233