

**40 dB Gain 0.8 dB NF Low Noise High Gain Amplifier
 Operating From 10 MHz to 1,000 MHz with 18 dBm
 P1dB and SMA**

SLNA-010-40-08-SMA is a wideband low noise RF coaxial power amplifier operating in the 10 MHz to 1 GHz frequency range. The amplifier offers 0.8 dB typical noise figure, 18 dBm of P1dB and 40 dB small signal gain with the excellent gain flatness of ± 1 dB. This exceptional technical performance is achieved through the use of hybrid MIC design and advanced GaAs PHEMT devices. The low noise amplifier requires typically a +12V DC power supply. The connectorized SMA module is unconditionally stable and includes built-in voltage regulation, bias sequencing, and reverse bias protection for added reliability. The amplifier operates over the temperature range of -40°C and +85°C.

Electrical Specifications (TA = +25°C , DC Voltage = 12Volts , DC Current = 110mA)

Description	Min	Typ	Max	Unit
Frequency Range	10		1,000	MHz
Small Signal Gain	37	40		dB
Gain Flatness		± 1	± 1.25	dB
Gain Variance at OTR*		1.25		dB
Output at 1 dB Compression Point	+16	+18		dBm
Output at 1 dB Compression Point	+16	+18		dBm
Noise Figure (50 MHz to 1,000 MHz)		0.8	1	dB
Input VSWR		1.45:1	1.65:1	
Output VSWR		1.3:1	1.5:1	
Reverse Isolation	50	55		dB
Operating DC Voltage	10	12	15	Volts
Operating DC Current	100	110	125	mA
Operating Temperature Range	-40		+85	°C

*OTR= Base Plate Operating Temperature Range

Absolute Maximum Rating

Parameter	Rating	Units
Source Voltage	+15	Volts
RF input Power	+13	dBm
Operating Temperature (base-plate)	-40 to +85	°C
Storage Temperature	-55 to +125	°C



ESD Sensitive Material, Transport material in Approved ESD bags. Handle only in approved ESD Workstation.

Mechanical Specifications

Size	
Length	1.5 in [38.1 mm]
Width	0.85 in [21.59 mm]
Height	0.375 in [9.53 mm]
Input Connector	SMA Female
Output Connector	SMA Female



Features:

- 10 MHz to 1 GHz Frequency Range
- P1dB: 18 dBm
- Flat Small Signal Gain: 40 dB
- Gain Flatness: ± 1 dB
- Noise Figure: 0.8dB typ
- Reverse Isolation: 55 dB
- 50 Ohm Input and Output Matched
- -40 to 85°C Operating Temperature
- Unconditionally Stable
- Regulated Supply & Bias Sequencing
- Overvoltage Protection

Applications:

- Laboratory Applications
- R&D Labs
- Military Radio
- Radar Systems
- Telecom Infrastructure
- Test Instrumentation
- Military & Space
- Communication Systems
- Wireless Communication
- Microwave Radio Systems
- Cellular Base Stations
- Low Noise Amplifier
- General Purpose Amplification
- General Purpose Wireless
- Wideband Gain Block
- IF Amplifier/RF Driver Amplifier
- RF Wideband Front Ends
- RF Pre-amplification

Fairview Microwave
 1130 Junction Dr. #100
 Allen, TX 75013
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Environmental Specifications

Temperature

Operating Range -40 to +85 deg C
Storage Range -55 to +125 deg C


Compliance Certifications (visit www.FairviewMicrowave.com for current document)

RoHS Compliant Yes



Plotted and Other Data

Notes:

- Values at 25 °C, sea level
- ESD Sensitive Material, Transport material in Approved ESD bags. Handle only in approved ESD Workstation.



Typical Performance Data





40 dB Gain 0.8 dB NF Low Noise High Gain Amplifier Operating From 10 MHz to 1,000 MHz with 18 dBm P1dB and SMA from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [40 dB Gain 0.8 dB NF Low Noise High Gain Amplifier Operating From 10 MHz to 1,000 MHz with 18 dBm P1dB and SMA SLNA-010-40-08-SMA](#)

URL: <http://www.fairviewmicrowave.com/0.8db-nf-low-noise-amplifier-40db-slna-010-40-08-sma-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE 40 dB Gain 0.8 dB NF Low Noise High Gain Amplifier Operating From 10 MHz to 1,000 MHz with 18 dBm P1dB and SMA		DWG NO SLNA-010-40-08-SMA		CAGE CODE 3FKR5	
CAD FILE	040215	SHEET	SCALE	N/A	SIZE A 2233