

SM3557 DATA SHEET

TNC Female to BNC Male Adapter

TNC female to BNC male adapter part number SM3557 from Fairview Microwave is in-stock and ships same day. This Fairview TNC to BNC adapter has a female to male gender configuration. SM3557 TNC female to BNC male adapter operates to 8 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.25:1 maximum.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Μ

Description	Min	Тур	Мах	Units
Frequency Range	DC		8	GHz
VSWR			1.25:1	
Electrical Specification N Values at 25°C, sea leve				
chanical Specificatio	ons			
Size Length Width			1.69 in [42.93 mm] 0.56 in [14.22 mm]	
Weight			0.069 lbs [31.3 g]	
Description		Connector 1	Connector 2	
Туре		TNC Female	BNC Male	
Polarity		Standard	Standard	
Interface Specification		MIL-STD-348	MIL-STD-348	3

Material Specifications

Description	Connector 1	Connector 2 BNC Male	
Туре	TNC Female		
Contact Plating	Gold	Gold	
Contact Plating Spec.	MIL-G-45204	MIL-G-45204	
Outer Contact Material	Passivated Stainless Steel		
Body Material		Brass	
Body Plating		Nickel	
Body Plating Spec.		QQ-N-290	
Coupling Nut Material		Brass	
Coupling Nut Plating		Nickel	
Coupling Nut Plating Spec.		QQ-N-290	



Configuration:

- TNC Female Connector 1
- BNC Male Connector 2
- 50 Ohm
- Straight Body Geometry

Features:

- VSWR of 1.25:1 max up to 8 GHz
- TNC interface meets MIL-STD-348
- BNC interface meets MIL-STD-348
- Contact plating according to MIL-G-45204

Applications:

- Enables Between Series
 Connections
- General Purpose Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Environmental Specifications

Temperature Operating Range

-65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data



TNC Female to BNC Male Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: TNC Female to BNC Male Adapter SM3557

URL: https://www.fairviewmicrowave.com/tnc-female-bnc-male-adapter-sm3557-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





3FKR5

7361



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689