



SMA Male to 2.92mm Male Adapter

SMA male to 2.92mm male adapter part number SM3290 from Fairview Microwave is in-stock and ships same day. This Fairview SMA to 2.92mm adapter has a male to male gender configuration and is built of durable stainless steel. SM3290 SMA male to 2.92mm male adapter operates to 27 GHz. The SMA connector mates mechanically with commercially available 3.5mm and 2.92mm (K) connectors. The Fairview Microwave RF adapter provides excellent VSWR of 1.2:1 maximum.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		27	GHz
VSWR			1.2:1	

Electrical Specification Notes: Values at 25°C, sea level.

Mechanical Specifications

Size

 Length
 0.751 in [19.08 mm]

 Weight
 0.0136 lbs [6.17 g]

Description	Connector 1	Connector 2
Description	Connector 1	Connector 2
Туре	SMA Male	2.92mm Male
Polarity	Standard	Standard
Mating Cycles	500	500
Mating Torque	8 to 10 in-lbs	8 to 10 in-lbs
	[0.90 to 1.13 Nm]	[0.90 to 1.13 Nm]



Configuration:

- SMA Male Connector 1
- 2.92mm Male Connector 2
- 50 Ohms
- Straight Body Geometry

Features:

- VSWR of 1.2:1 max up to 27 GHz
- Contact plating according to MIL-G-45204
- Gold over Nickel Plated Beryllium Copper Contact

Applications:

- Enables Between Series Connections
- General Purpose Test

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689





Material Specifications

Description	Connector 1	Connector 2			
Туре	SMA Male	2.92mm Male			
Contact Material	Beryllium Copper	Beryllium Copper			
Contact Plating	Gold over Nickel	Gold over Nickel			
Contact Plating Spec.	MIL-G-45204	MIL-G-45204			
Insulation Material	PTFE	PTFE			
Body Material	Passivated Stainless Steel	Passivated Stainless Steel			
Body Plating Spec.	ASTM A380	ASTM A380			
Coupling Nut Material	Passivated Stainless Steel	Passivated Stainless Steel			
Coupling Nut Plating Spec.	ASTM A380	ASTM A380			

Environmental Specifications

Temperature

Operating Range Vibration Salt Spray -55 to +100 deg C


MIL-STD 202, Method 204, Condition D (20 G's) MIL-STD 202, Method 101, Condition B, 5% salt solution

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data







SMA Male to 2.92mm Male Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order


For additional information on this product, please click the following link: SMA Male to 2.92mm Male Adapter SM3290

URL: https://www.fairviewmicrowave.com/sma-male-2.92mm-male-adapter-sm3290-p.aspx

		w Microwave does	-	-	
		y particular purpos			
t of the use of			,		







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
SMA Male to 2.92mm Male Adapter	DWG NO SM3290 CAG			CAGE C	3FKR5	
	CAD FILE 111615	SHEET	SCAL	E N/A	SIZE A	150