

SMB-BNC ADAPTERS 4GHZ

SM3632


SPECIFICATIONS

ELECTRICAL


FREQUENCY: 0-4 GHZ
 IMPEDANCE: 50 OHMS
 VSWR: 1.2:1 MAX @ 2GHZ
 1.35:1 MAX @ 4 GHZ

MECHANICAL

MATERIAL BODY: NICKEL PLATED BRASS
 CONTACTS: BeCu
 CONTACT PLATING: Au PER MIL-G-45204
 INSULATOR: TEFLON
 INTERFACE: MIL-STD-348A
 TEMPERATURE: -65° +125°C



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMB-BNC ADAPTERS 4GHZ

| | | | |
|----------|-----------|--------|----------|
| SIZE | CAGE CODE | DWG NO | REV |
| A | 3FKR5 | SM3632 | A |
| SCALE | | SHEET | |