


RA 1.85mm Female to 2.92mm Female Adapter

Electrical Specifications

Frequency Range Maximum VSWR Maximum Insertion Loss DC to 40 GHz 1.3:1 0.35 dB

Specifications by Frequency



www.fairviewmicrowave.com sales@fairviewmicrowave.com

SM3846 DATA SHEET

REV 1 Page 1 of 3 Copyright © 2014





RA 1.85mm Female to 2.92mm Female Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: RA 1.85mm Female to 2.92mm Female Adapter SM3846


URL: http://www.fairviewmicrowave.com/ra-1.85mm-female-2.92mm-female-adapter-sm3846-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warnaty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







FAIRVIEW MICROWAVE INC.	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
RAE1.85mm Female to 2.92mm Female Adapter 1.85mm Female to 2.4mm Female Right Angle	DWG NO SM3846			CAGE CODE 3FKR5		
Adapter	CAD FILE 030314	SHEET	SCAL	E N/A	SIZE A	2233

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689