

## SM4073 DATA SHEET

# Low PIM N Female to N Female Adapter With Body Flats

Low PIM type N female to type N female adapter part number SM4073 from Fairview Microwave is in-stock and ships same day. This Fairview type N to type N adapter has a female to female gender configuration in a Low PIM design. SM4073 type N female to type N female adapter operates to 6 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.2:1 maximum and passive intermodulation of -155 dBc maximum.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

## **Electrical Specifications**

Description	Min	Тур	Max	Units
Frequency Range	DC		6	GHz
VSWR			1.2:1	
Passive Intermodulation			-155	dBc
(using 2x20W tones)				
Operating Voltage (AC)			1,000	Vrms
DWV (AC)			2,500	Vrms

**Electrical Specification Notes:** 

Values at 25°C, sea level.

#### **Mechanical Specifications**

Size Length Width Weight

1.5 in [38.1 mm] 0.55 in [13.97 mm] 0.08774 lbs [39.8 q]

Description	Connector 1	Connector 2		
Туре	N Female	N Female		
Polarity	Standard	Standard		
Interface Specification	IEC 169-16	IEC 169-16		
Mating Cycles	500	500		



## **Configuration:**

- N Female Connector 1
- N Female Connector 2
- 50 Ohms
- Low PIM Design
- Straight Body Geometry

#### **Features:**

- VSWR of 1.2:1 max up to 6 GHz
- PIM levels better than -155 dBc
- N interface meets IEC 169-16
- 5 µm minimum contact plating
- Silver Plated Beryllium Copper Contact

## **Applications:**

General Purpose Test

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





### **Material Specifications**

Description	Connector 1	Connector 2		
Туре	N Female	N Female		
Contact Material	Beryllium Copper	Beryllium Copper		
Contact Plating	Silver	Silver		
Contact Plating Spec.	5 µm minimum	5 µm minimum		
Insulation Material	PTFE	PTFE		
Outer Contact Material	Brass	Brass		
Outer Contact Plating	Tri-Metal	Tri-Metal		

## **Environmental Specifications**

**Temperature** 

Operating Range


-45 to +125 deg C

**Compliance Certifications** (see product page for current document)

### **Plotted and Other Data**

Notes:

## **Typical Performance Data**







Low PIM N Female to N Female Adapter With Body Flats from Fairview Microwave is in-stock and available to ship sameday. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: Low PIM N Female to N Female Adapter With Body Flats SM4073

URL: https://www.fairviewmicrowave.com/low-pim-n-female-n-female-adapter-sm4073-p.aspx









FAIRVIEW MICROWAVE INC.  ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  3. DIMENSIONS ARE IN INCHES [mm].					
Low PIM N Female to N Female Adapter With Body Flats	DWG NO SM4073			CAGE CODE 3FKR5		
	CAD FILE 111814	SHEET	SCALE	N/A	SIZE A	150