

BNC T Adapter Female (Jack) Male (Plug) Female (Jack), Nickel Plated Brass Body

BNC T adapter female-male-female part number SM3448 from Fairview Microwave is in-stock and ships same day. This Fairview BNC T adapter has a female-male-female gender configuration. Our BNC T connector operates to 4 GHz.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		4	GHz
Operating Voltage (DC)			500	Vdc
DWV (AC)			1,500	Vrms

Electrical Specification Notes:
 Values at 25°C, sea level.

Mechanical Specifications

Size	
Length	1.280 in [32.5 mm]
Width	1.03 in [26.16 mm]
Weight	0.043 lbs [19.5 g]

Description	Connector 1	Connector 2
Type	BNC Female	BNC Male
Polarity	Standard	Standard
Interface Specification	MIL-STD-348	MIL-STD-348

Material Specifications

Description	Connector 1	Connector 2
Type	BNC Female	BNC Male
Contact Material	Beryllium Copper	Brass
Contact Plating	Silver	Silver
Contact Plating Spec.	QQ-S-365	QQ-S-365
Insulation Material	PTFE	PTFE
Outer Contact Material	Brass	
Outer Contact Plating	Nickel	
Outer Contact Plating Spec.	QQ-N-290	
Body Material		Brass
Body Plating		Nickel
Body Plating Spec.		QQ-N-290



Configuration:

- BNC Female Connector 1
- BNC Male Connector 2
- 50 Ohm
- Tee Body Geometry

Features:

- BNC interface meets MIL-STD-348
- Contact plating according to QQ-S-365

Applications:

- General Purpose Test

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Environmental Specifications

Temperature

Operating Range -65 to +165 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data


Notes:

BNC T Adapter Female (Jack) Male (Plug) Female (Jack), Nickel Plated Brass Body from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [BNC T Adapter Female \(Jack\) Male \(Plug\) Female \(Jack\), Nickel Plated Brass Body SM3448](#)

URL: <https://www.fairviewmicrowave.com/bnc-female-male-female-tee-adapter-sm3448-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



STANDARD TOLERANCES	
.X	±0.2
.XX	±0.01
.XXX	±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

<p>Fairview Microwave™ an INFINIT[®] brand</p>	<p>NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].</p>			
	<p>TITLE BNC T Adapter Female (Jack) Male (Plug) Female (Jack), Nickel Plated Brass Body</p>		<p>DWG NO SM3448</p>	<p>CAGE CODE 3FKR5</p>
<p>CAD FILE 111416</p>	<p>SHEET</p>	<p>SCALE N/A</p>	<p>SIZE A</p>	<p>41742</p>